

## 2U Hinged Solid Blank Rack Panel

Product ID: RKP NLHS2U



The RKP NLHS2U 2U Hinged Solid Blank Rack Panel mounts to a standard 19" 2 or 4-post rack to improve the organization and appearance of your rack, while maintaining easy access and helping to guide airflow. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The hinged blanking panel is reversible, meaning it can be installed to open from either the left or right side for easy access to the inside of your rack, while still covering the unused rack spaces for a professional look.

The filler panel is made of high-quality steel for long-term durability, plus the solid design helps to guide airflow along the back of the rack instead of passing through. For easy installation, this rack panel comes complete with rack installation screws (10-32).

For a vented panel, please see our [2U Hinged & Vented Rack Blank Panel](#) (RKP NLHV2U).

Backed by a StarTech.com 2-year warranty.

### Certifications, Reports and Compatibility



### Applications

- Fill in unused gaps between equipment in server racks and cabinets, while still allowing access to the inside of the rack

### Features

- Hinged for easy access to rack components
- Reversible - install to open from the left or right side
- TAA compliant for GSA Schedule purchases
- 2U solid rack panel design
- Sturdy steel construction
- Mounts to standard 19" 2 or 4-post server racks
- Includes rack screws

<b>Hardware</b>	Warranty	2 Years
	Airflow Rate	Solid
	Industry Standards	EIA RS310-D
	Mounting Options	Front Mount (Front Only)
	U Height	2U
<b>Physical Characteristics</b>	Color	Black
	Enclosure Type	Steel
	Weight of Product	19.6 oz [554.5 g]
<b>Packaging Information</b>	Package Height	1.6 in [40 mm]
	Package Length	19.9 in [50.5 cm]
	Package Width	3.9 in [10 cm]
	Shipping (Package) Weight	23.2 oz [658.6 g]
<b>What's in the Box</b>	Included in Package	1 - 2U Hinged Solid Rack Panel
		2 - 5/8" #10-32 UNF Screws
		2 - #10-32 UNF Cage Nuts

Product appearance and specifications are subject to change without notice.