

# Solid Blank Panel with Hinge for Server Racks - 6U

Product ID: RKP NLHS6U



You can improve the appearance and airflow of any standard 19-inch server rack, while maintaining easy access, using this 6U blanking panel. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

## Professional look

The hinged blanking panel creates a clean and professional look by covering empty space and visible cables. Adding blanking panels to your server racks offers a tidier appearance for a more organized server room.

## Easy access to your rack-mounted equipment

The blanking panel features a hinged design that enables you to open the panel for fast and easy server access. You can quickly open the panel, make your required adjustments and when you're finished, simply close the panel to restore the professional appearance and order of your server room. The panel is reversible, so you can install it on the left or the right side of your rack.

Plus, the panel includes the screws and nuts you will need to install it in your server rack, to ensure a quick and easy installation.

### **Improve airflow**

The blanking panel features a solid design that helps guide airflow down the back of your rack, rather than between occupied spaces. Improved airflow helps ensure your rack-mounted equipment is running at an optimal temperature.

The RKPNLHS6U is backed by a 2-year StarTech.com warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Fill in unused gaps between equipment in server racks and cabinets
- Access your covered rack with an open-and-shut design
- Help guide the airflow along the back of your rack, instead of passing through your equipment

### Features

- Create a tidy and professional look by covering unused rack space
- Easily access rack components by opening the hinged panel
- TAA compliant for GSA Schedule purchases
- Versatile installation options with a reversible blank panel that can open from the left or the right side
- 6U, solid rack-panel design
- Mounts to standard 19" 2 or 4-post racks
- Sturdy steel construction
- Rack screws and nuts included

|                                 |                           |                                |
|---------------------------------|---------------------------|--------------------------------|
| <b>Hardware</b>                 | Warranty                  | 2 Years                        |
|                                 | Airflow Rate              | Solid                          |
|                                 | Industry Standards        | EIA RS310-D                    |
|                                 | Mounting Options          | Front Mount (Front Only)       |
|                                 | U Height                  | 6U                             |
| <b>Physical Characteristics</b> | Color                     | Black                          |
|                                 | Product Height            | 0.6 in [1.5 cm]                |
|                                 | Product Length            | 18.3 in [46.5 cm]              |
|                                 | Product Width             | 10.4 in [26.5 cm]              |
|                                 | Weight of Product         | 3.2 lb [1.5 kg]                |
| <b>Packaging Information</b>    | Package Height            | 1.5 in [38 mm]                 |
|                                 | Package Length            | 21.1 in [53.5 cm]              |
|                                 | Package Width             | 11.3 in [28.6 cm]              |
|                                 | Shipping (Package) Weight | 3.8 lb [1.7 kg]                |
| <b>What's in the Box</b>        | Included in Package       | 1 - 6U Hinged Solid Rack Panel |
|                                 |                           | 4 - 5/8" #10-32 UNF Screws     |
|                                 |                           | 4 - #10-32 UNF Cage Nuts       |
|                                 |                           | 1 - Instruction manual         |

Product appearance and specifications are subject to change without notice.