

# Vented Blank Panel with Hinge for Server Racks - 6U

Product ID: RKP NLHV6U



You can improve the appearance and airflow of any standard 19-inch server rack while still enjoying easy access to unused space, using this 6U hinged blanking panel. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

## Professional look

The blanking panel creates a clean and professional look by covering empty space and visible cables. Adding blanking panels to your server racks offers a tidier appearance for a more organized server room.

## Maximize airflow

The blanking panel features a vented design enabling unobstructed airflow through your rack. The vented panel maximizes airflow to help ensure your equipment is running at an optimal temperature.

## **Hassle-free access**

With a hinged design, you can quickly open the blanking panel, make your required adjustments and when you're finished, simply close the panel to restore the professional appearance and order of your server room. The panel is reversible, so you to install it on the left or the right side of your rack, to best suit your needs. The rack panel also comes complete with rack installation screws and nuts, giving you everything you need to ensure a hassle-free installation.

The RKP NLHV6U is backed by a 2-year StarTech.com warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Fill in unused gaps between equipment in server racks and cabinets
- Access your covered rack with an open-and-shut design
- Increase the airflow in your server rack with vented design that helps keep your equipment running at an optimal temperature

### Features

- Create a tidy and professional look by covering empty rack space
- Easily access rack components with the built-in hinge
- TAA compliant for GSA Schedule purchases
- Versatile installation options with a reversible blank panel that can open from the left or the right side
- 6U panel that mounts to any standard 19 in. 2 or 4-post rack
- Sturdy steel construction
- Rack screws and nuts included

<b>Hardware</b>	Warranty	2 Years
	Industry Standards	EIA RS310-D
	Mounting Options	Front Mount (Front Only)
	U Height	6U
<b>Physical Characteristics</b>	Color	Black
	Product Height	0.6 in [15 mm]
	Product Length	19 in [483 mm]
	Product Weight	30.3 oz [857.5 g]
	Product Width	10.4 in [265 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	2.4 lb [1.1 kg]
<b>What's in the Box</b>	Included in Package	1 - 6U Hinged Vented Rack Panel
		4 - 5/8" #10-32 UNF screws
		4 - #10-32 UNF cage nuts

Product appearance and specifications are subject to change without notice.