

12U Rack Enclosure Server Cabinet - 21 in. Deep - Wood Finish - Flat Pack

Product ID: RKWOODCAB12



The RKWOODCAB12 12U Office Server Cabinet lets you store your server, network or AV equipment discreetly in the office, with a stylish wood finish. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Designed to blend in with your office or boardroom furniture, this 12U server cabinet features wood laminate exterior panels with a shaded glass front window that keeps your equipment visible for monitoring, as well as front and rear key-locks to prevent unauthorized access. To help keep your valuable equipment running cooler, we've included a ventilation panel to maximize airflow. The cabinet also features durable casters, so that positioning your server equipment as needed isn't a hassle.

The 4-post enclosed rack supports a weight capacity of up to 300lbs (136kg) and offers rails with adjustable mounting depth from 17in (423mm) to 21in (523mm) to accommodate various sizes of equipment. Making it easy to route your cables where you need them, the 12U cabinet offers cable grommets on the rear and top panels, and a cable entry panel at the base.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Mount server or networking equipment in a well-furnished boardroom
- Add an attractive server cabinet that won't be an eyesore in small / home-office areas with limited space

Features

- 12U Enclosed cabinet with a stylish wood finish
- Supports a weight capacity of up to 300lbs (136kg)
- TAA compliant for GSA Schedule purchases
- Adjustable mounting depth from 16.7in (423mm) to 20.6in (523mm)
- Ventilation and cable entry panels
- Casters included
- Front and rear key-lock
- Flat-packed for easy shipping

Hardware	Warranty	2 Years
	Fan Options	Two Optional Fans: 92 mm
	Frame Type	Enclosed Cabinet
	Front Door Construction	Wood with Glass Window
	Front Door Features	Secure Key Lock with Reversible and Removable Front Door
	Industry Standards	EIA/ECA-310-E
	Mounting Hole Types	Square (For Cage Nut)
	Mounting Rail Profile	L-Shape
	Rack Type	4-Post
	Rear Door Construction	Wood
	Side Panel Construction	Wood
	Special Features	Adjustable Mounting Rails Casters (Included) Easy Assembly Leveling Feet
	U Height	12U
Wallmountable	No	
Performance	Weight Capacity (Stationary)	300.7 lb [136.1 kg]
Physical Characteristics	Color	Black & Brown
	Rear Door Features	Secure Key Lock with Removable Back Door
Product Measurements	Internal Depth	25.1 in [63.7 cm]
	Internal Width	20.5 in [52.1 cm]
	Maximum Mounting Depth	20.6 in [52.2 cm]
	Minimum Mounting Depth	16.6 in [42.2 cm]
	Product Height	25.6 in [65 cm]
	Product Height with Casters	28.4 in [72.1 cm]
	Product Length	26 in [66 cm]
	Product Width	22 in [56 cm]
Weight of Product	67.8 lb [30.7 kg]	
Packaging Information	Flat Pack (Assembly Required)	Yes

	Package Height	1.8 in [46 mm]
	Package Length	29.6 in [75.3 cm]
	Package Width	29.6 in [75.3 cm]
	Shipping (Package) Weight	76.7 lb [34.7 kg]
What's in the Box	Included in Package	<ul style="list-style-type: none"> 1 - Right Side Panel 1 - Left Side Panel 1 - Rack Top 1 - Rack Bottom 1 - Rear Panel 1 - Front Door 4 - Rack Rails 2 - Front/Rear Support 1 - Ventilation Panel 1 - Cable Entry Panel 4 - Panel Brackets 1 - Strike Plate 1 - Round Grommet 2 - Locking Latches (with 2 keys each) 4 - Casters 32 - M6x12 Screws 8 - M5x12 Screws 2 - M4x12 Screws 4 - M6x15 12 - Cams 12 - Connecting Bolts 16 - Dowel Pins 30 - M5 Screws 30 - M5 Cage Nuts 1 - Instruction Manual

Product appearance and specifications are subject to change without notice.