

USB 3.0 SATA Hard Drive Duplicator & Eraser Dock - Standalone 2.5/3.5in HDD & SSD Eraser and Cloner

Product ID: SATDOCK2REU3



The SATDOCK2REU3 USB 3.0 Standalone Duplicator and Eraser Dock lets you connect your 2.5in/3.5in SATA HDDs or SSDs through SuperSpeed USB 3.0, with the ability to swap drives in and out as needed. The dock also functions as a standalone drive duplicator and eraser – an efficient and versatile solution for external drive management.

Featuring standalone Sector by Sector hard drive duplication with built-in LED progress bar, and support for 2 drive single pass over writing the SATDOCK22EU3 is a user-friendly all-in-one solution for any application requiring hard drive duplication or erasing.

With support for SATA I/II/III, and large capacity drives (tested up to 4TB) this HDD/SSD docking station is compatible with virtually any SATA hard drive, and greatly increases the storage/backup capabilities of your computer.

Extend the value of this hard drive docking station further with the addition of our [SATA to IDE Hard Drive Adapter](#) (SAT2IDEADP), allowing easy insertion of any 2.5 or 3.5in. IDE hard drive into a SATA hard drive dock.

The SATDOCK2REU3 is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- System administrators who need quick access to drives for imaging
- Data Archiving
- Technicians who regularly test or benchmark different hard drives and need to swap between them
- Forensic investigators who require disk sector imaging/cloning to create an exact replica of a source drive onto a different drive
- Professionals who require identical backups for when data integrity is crucial, such as data recovery
- Cloning hard drives that contain hidden partitions, that some software disk cloning programs may skip
- IT administrators that wish to quickly clear/erase a drive in preparation for use in other applications
- Data recovery specialists who need quick access to drives to recover/retrieve data

Features

- Supports 2.5in and 3.5in form factor SATA hard drives (HDD) and solid state drives (SSD)
- Standalone Sector-by-Sector hard drive duplication
- Stand alone single pass overwrite erase
- SuperSpeed USB 3.0 compliant host interface, with up to 5 Gbps of data bandwidth
- High Speed USB 2.0 compliant host interface, with transfer rates up to 480Mbps
- Supports SATA revision I/II/III (1.5/3.0/6.0 Gbps) drives
- Plug-and-Play and Hot-Swap compatible
- Universal Power Adapter (NA/UK/EU)
- Built-in LED progress bar

Hardware	Warranty	2 Years
	Chipset ID	Prolific - PL2775
	Compatible Drive Types	SATA
	Drive Installation	Removable
	Drive Size	2.5in & 3.5in
	Fan(s)	No
	Interface	USB 3.0
	Number of Drives	2
Performance	Max Drive Capacity	Currently tested with up to 4TB 7200 RPM 3.5" hard drives and 1TB 7200 RPM 2.5" hard drives
	Type and Rate	USB 3.0 - 5 Gbit/s SATA II (3 Gbps)
Connector(s)	Drive Connectors	2 - SATA Data & Power Combo (7+15 pin)
	Host Connectors	1 - USB Type-B (9 pin) USB 3.0
Software	OS Compatibility	OS independent; No software or drivers required
Special Notes / Requirements	Note	Destination drive must be the same size or larger than the source drive
Indicators	LED Indicators	1 - HDD1 / 75%
		1 - HDD2 / 100%
		1 - Link / 25%
		1 - Power / 50%
Power	Center Tip Polarity	Positive
	Input Current	1.2A
	Input Voltage	110V-240V AC
	Output Current	3000mA
	Output Voltage	12 DC
	Plug Type	M
	Power Consumption (In Watts)	36
	Power Source	AC Adapter Included
Environmental	Humidity	5-90%
	Operating Temperature	0°C to 85°C (32°F to 185°F)
	Storage Temperature	-10°C to 95°C (14°F to 203°F)

Physical Characteristics	Product Height	2.4 in [62 mm]
	Product Length	5 in [128 mm]
	Product Weight	21.5 oz [610 g]
	Product Width	4.1 in [103 mm]
Packaging Information	Shipping (Package) Weight	25.1 oz [710 g]
What's in the Box	Included in Package	1 - HDD Dock
		1 - USB 3.0 Cable
		1 - Universal power adapter: comes ready for NA/EU/UK only when you buy in NA/EU/UK; comes ready for Australia and New Zealand only when you buy in Australia and New Zealand
		1 - User Manual

Product appearance and specifications are subject to change without notice.