

Drive Eraser and Dock for 2.5 / 3.5in SATA SSD / HDD - USB 3.0

Product ID: SDOCK1EU3P



Make the most of your SATA drives. This standalone eraser dock lets you erase your 2.5" and 3.5" solid-state drives or hard drives without connecting to a host computer, making it easy to re-use or re-purpose your SATA drive. For added peace of mind, the dock offers a printed confirmation when data has been securely erased.

The eraser dock also gives you a single-bay dock for your SATA drive with fast USB 3.0 performance, also known as USB 3.1 Gen 1 (5 Gbps).



Industry-recognized erase modes

Using industry-recognized erase modes, you can rest assured that the standalone eraser securely cleans, erases or sanitizes the data from your 2.5" or 3.5" SSD or HDD.

The eraser dock supports nine erase modes including Quick Erase, Single and Multi-pass Overwrites, Custom Erase, Secure Erase and Enhanced Secure Erase. The Multi-pass Overwrite (3-Pass Full Disk Overwrite) erase procedures meet the requirements of DoD (5220.22-M) standards.

Wipe sensitive data securely, confirmed with a printed receipt

The eraser dock lets you connect to an RS232 serial printer to print a record of the erase procedure and confirm that the erase has been successfully completed. This feature is ideal for IT technicians, system administrators or any departments needing confirmation when erasing sensitive or confidential information. For your reference, the printed receipt clearly shows you the time and date of erase, as well as the erase mode used.

Easy drive management and wide compatibility

For IT technicians or business professionals who need to check files or test different hard drives, the dock lets you hot-swap drives in and out as needed. The dock features a single SATA bay with a top-loading design for easy access to your drives, which makes it easy to quickly back-up or transfer data to a hard drive or solid-state drive.

With support for SATA I and II and large capacity drives (tested up to 6TB), this docking station is compatible with virtually any 2.5" and 3.5" SATA SSD or HDD drive.

The eraser dock also works with 2.5" and 3.5" IDE hard drives, mSATA drives and M.2 drives using a compatible StarTech.com adapter:

IDE hard drives: Use StarTech.com adapter [SAT2IDEADP SATA to 2.5in or 3.5in IDE Hard Drive Adapter for HDD Docks](#)

mSATA drives: Use StarTech.com adapter [SAT32MSAT257 mSATA SSD to 2.5in SATA Adapter Converter](#)

M.2 drives: Use StarTech.com adapter [SAT32M225 M.2 NGFF SSD to 2.5in SATA Adapter Converter](#)

Hassle-free set-up and a compact design

The eraser dock is OS independent, which ensures a quick and easy setup. Its compact design and small footprint allows it to tuck easily into your workspace.

The TAA compliant SDOCK1EU3P is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- IT technicians and business professionals who wish to quickly and securely erase data to repurpose SSDs or HDDs
- System administrators, IT professionals and business administrators who need quick access to drives
- IT technicians who regularly test or benchmark different hard drives and need to swap between them

Features

- Easy-to-use secure erasing with no host device required
- Supports a serial printer (RS232) for receipt printing and erase confirmation
- Fast access to files through USB 3.0 (5 Gbps)
- Supports most 2.5" and 3.5" SATA HDD and SSD drives
- Also supports 2.5" and 3.5" IDE hard drives, mSATA drives and M.2 drives, using a compatible StarTech.com adapter
- TAA compliant
- 9 modes of erase including: Quick and Secure Erase, Single Pass Overwrite and Multi-pass Overwrites - meets DoD (5220.22-M) standards
- Supports SATA I and II
- Plug-and-play installation
- Supports drive hot-swapping
- Built-in LCD display and menu navigation buttons
- Power and activity LED

Hardware	Warranty	2 Years
	Bus Type	USB 3.0
	Compatible Drive Types	SATA
	Drive Size	2.5in & 3.5in
	Interface	USB 3.0
	Number of Drives	2
Performance	Erase Modes	Quick Erase
		1-Pass Overwrite (NIST SP 800-88 Rev 1 - Clear)
		3-Pass Overwrite
		7-Pass Overwrite
		Custom Erase
		Secure Erase (NIST SP 800-88 Rev 1 - Purge)
		Enhanced Secure Erase (NIST SP 800-88 Rev 1 - Purge)
	Hot Swap Capability	Yes
	Max Drive Capacity	Currently tested with up to 6TB 7200 RPM
	Maximum Data Transfer Rate Type and Rate	3Gbps
USB 3.0 - 5 Gbit/s SATA II (3 Gbps)		
Connector(s)	Drive Connectors	2 - SATA Data & Power Combo (7+15 pin) Receptacle
	Host Connectors	1 - USB Type-B (9 pin) USB 3.0 Female
	Other Interface(s)	1 - DB 9-pin Serial Male
Software	OS Compatibility	OS independent; No software or drivers required
Special Notes / Requirements	Note	Receipt printing through the RS232 serial port requires a printer which supports the ESC/P printer control language.
Indicators	LED Indicators	1 - 2-Line LCD display on top
		1 - Power & Activity LED
		1 - HPA/DCO Detect LED
Power	Input Current	1.4 A
	Input Voltage	100 - 240 AC
	Output Current	5 A
	Output Voltage	12 DC
	Power Consumption (In Watts)	60

	Power Source	AC Adapter Included
Environmental	Humidity	10% ~ 90% RH
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-10°C to 65°C (14°F to 149°F)
Physical Characteristics	Color	Black
	Enclosure Type	Plastic
	Product Height	2.8 in [7 cm]
	Product Length	5.5 in [14 cm]
	Product Width	4.8 in [12.3 cm]
	Weight of Product	23.2 oz [656 g]
Packaging Information	Package Height	3.6 in [91 mm]
	Package Length	14.8 in [37.6 cm]
	Package Width	7.4 in [18.9 cm]
	Shipping (Package) Weight	4.5 lb [2 kg]
What's in the Box	Included in Package	1 - hard drive eraser and USB 3.0 dock
		1 - USB 3.0 cable
		1 - universal power adapter
		4 - power adapter plug (NA/EU/UK/AU)
		1 - quick start guide

Product appearance and specifications are subject to change without notice.