

4-Bay Hard Drive Docking Station for 2.5"/3.5" SSDs and HDDs - eSATA/USB 3.0 to SATA (6Gbps)

Product ID: SDOCK4U33E



Dock and swap up to four drives from your laptop or desktop computer simultaneously, using a single eSATA or USB port. This 4-bay docking station gives you large data capacity and fast file transfers with support for SATA I, II and III (up to 6Gbps).

Large data capacity with four drive bays

Access multiple drives with this quad-bay docking station. It saves you valuable time every day by giving you independent access to four 2.5" or 3.5" SATA hard drives or solid-state drives. Ideal for data recoveries, imaging or backups, it lets you access four drives at once, instead of connecting your drives one by one.

Versatile connection options with fast data transfers

You can connect the docking station through either eSATA or USB. For fast performance and efficient data transfers when connected through eSATA, the docking station supports full SATA III transfer speeds - up to 6Gbps. For universal compatibility, the dock can be connected through USB 3.0 with transfer speeds up to 5Gbps, plus it supports UASP for enhanced performance.

Easy drive management and wide compatibility

For IT technicians or business professionals who need to check files or test different drives, the dock lets you hot-swap your drives in and out as needed. Its top-loading, toaster-style design with drive ejection buttons make the dock easy to use while two silent cooling fans help to dissipate heat to maintain an optimum operating temperature.

With support for SATA I, II and III high-capacity drives (tested up to 6TB), this docking station is compatible with virtually any 2.5" and 3.5" SATA SSD or HDD drive.



The docking station also works with 2.5" and 3.5" IDE hard drives, mSATA drives and M.2 drives using a compatible StarTech.com adapter:

IDE hard drives: Use StarTech.com adapter [SAT2IDEADP SATA to 2.5in or 3.5in IDE Hard Drive Adapter for HDD Docks](#)

mSATA drives: Use StarTech.com adapter [SAT32MSAT257 mSATA SSD to 2.5in SATA Adapter Converter](#)

M.2 drives: Use StarTech.com adapter [SAT32M225 M.2 NGFF SSD to 2.5in SATA Adapter Converter](#)

Hassle-free setup

The quad-bay dock is OS independent, which ensures a quick and easy setup. It also features a compact design and small footprint that makes it easy to tuck into your workspace.

The SDOCK4U33E is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- System builders and IT specialists can gain quick access to drives for imaging
- Back up data quickly to an external drive for archiving
- Transfer data from one drive to another
- Technicians can test or benchmark multiple drives with ease
- Backup important data and easily take the drive to an offsite location for safekeeping

Features

- Access up to four SATA drives simultaneously, in a single docking station
- Supports both 2.5" and 3.5" HDDs and SSDs
- USB 3.0 or high-speed eSATA host connection with port multiplier
- Supports SATA I, II and III (up to 6Gbps)
- Top-loading design with drive doors and drive ejection buttons
- UASP support for enhanced performance
- Dual 60mm cooling fans
- Backward compatible with USB 2.0 and 1.x
- Plug-and-play and hot-swap compatible

Hardware	Warranty	2 Years
	Chipset ID	JMicron - JMS567 JMicron - JBM575
	Compatible Drive Types	SATA
	Drive Installation	Removable
	Drive Size	2.5in & 3.5in
	Fan Bearing Type	Sleeve Bearing
	Fan(s)	Yes
	Fans	2 - 60 mm
	Interface	USB 3.0 & eSATA
	Number of Drives	4
Performance	Hot Swap Capability	Yes
	Max Drive Capacity	Currently tested with up to 6TB
	Maximum Data Transfer Rate	5Gbps
	MTBF	30000
	Port Multiplier	Yes
	Type and Rate	USB 3.0 - 5 Gbit/s SATA III (6 Gbps)
	UASP Support	Yes
Connector(s)	Drive Connectors	4 - 22 pin SATA Data & Power Combo Receptacle
	Host Connectors	1 - USB Type-B (9 pin) USB 3.0 Female 1 - eSATA (7 pin, Data) Plug
Software	OS Compatibility	OS independent; No software or drivers required
Indicators	LED Indicators	4 - Power 4 - Activity
Power	Input Current	2.0A
	Input Voltage	100 ~ 240 AC
	Output Current	6500mA
	Output Voltage	12 DC
	Plug Type	4-pin DIN
	Power Consumption (In Watts)	78
	Power Source	AC Adapter Included

Environmental	Humidity	20% ~ 80% RH
	Operating Temperature	5°C to 35°C (41°F to 95°F)
	Storage Temperature	-20°C to 50°C (-4°F to 122°F)
Physical Characteristics	Color	Black
	Enclosure Type	Plastic
	Product Height	3.4 in [87.3 mm]
	Product Length	11.2 in [285 mm]
	Product Weight	35.5 oz [1007 g]
	Product Width	6.8 in [172 mm]
Packaging Information	Shipping (Package) Weight	84.7 oz [2399 g]
What's in the Box	Included in Package	1 - 4-bay hard drive docking station
		1 - universal power adapter
		4 - power cords (NA/UK/EU/AU)
		1 - USB A to B cable
		1 - eSATA cable
		1 - quick install guide

Product appearance and specifications are subject to change without notice.