

Cisco SFP-H10GB-CU5M Compatible SFP+ 10-Gigabit Ethernet (10GbE) Passive Direct-Attach Twinax Cable - 5 m (16.4 ft)

Product ID: SFPCMM5M



The SFPCMM5M is a Cisco compatible direct-attach copper SFP+ cable that's designed, programmed and tested to work with Cisco® brand compatible switches and routers and complies with MSA industry standards.

This passive Twinax copper cable supports 10 Gigabit Ethernet applications connected through SFP+ (Mini-GBIC) ports. This copper SFP+ cable is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

Designed for high-speed performance, this low-power, low-latency SFP+ cable is a cost-effective alternative to fiber-optic cable assemblies, supporting short-distance applications such as point-to-point in-rack network switch or server connections.

StarTech.com SFP Cables

All StarTech.com SFP & SFP+ cables are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of direct-attach SFP cables and SFP modules, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility



Applications

- Use in 10Gb Ethernet and Fiber Channel applications
- Point-to-point in-rack and across rack network switch/server connections (Storage Area Networks (SAN), Network Attached Storage (NAS), Storage Servers, etc.)

Features

- 100% compatibility with Cisco equipment guaranteed
- StarTech.com SFP cables are backed by a lifetime warranty
- StarTech.com SFP cables are backed by a lifetime warranty
- Uses a cost-effective cabling alternative to fiber-optic setups
- Complies with Multi-Source Agreement (MSA) industry standards
- Low power consumption of less than .5 W
- Hot-swappable

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Compatible Brand	Cisco®
Performance	Compatible Networks	10 Gbps
	Impedance	100 Ohm
Connector(s)	Connector A	1 - SFP+ Latching Plug
	Connector B	1 - SFP+ Latching Plug
Power	Power Consumption (In Watts)	< 0.5 W
Environmental	Operating Temperature	0°C to 70°C
	Storage Temperature	-40°C to 80°C
Physical Characteristics	Cable Length	16.4 ft [5 m]
	Wire Gauge	24 AWG
Packaging Information	Package Height	0.8 in [20 mm]
	Package Length	13 in [33 cm]
	Package Quantity	1
	Package Width	10 in [25.5 cm]
	Shipping (Package) Weight	11.6 oz [328 g]
What's in the Box	Included in Package	1 - 5m SFP+ 10-Gigabit Ethernet (10GbE) Twinax Cable
	Product Height	0.5 in [1.2 cm]
	Product Length	16.4 ft [5 m]
	Product Width	0.6 in [14 mm]
	Weight of Product	11 oz [311 g]

Product appearance and specifications are subject to change without notice.