

4-Port PCIe Gigabit Network Adapter Card

Product ID: ST1000SPEX43



Now you can add four separate Gigabit network ports to your client, server or workstation through just one PCI Express slot, to provide connectivity to multiple networks without draining your budget.

Reliable connectivity to multiple networks

This 4-port network card delivers powerful connectivity for your business, corporate or government office environment, with support for high-performance, 4-channel networking and a maximum throughput of up to 1000Mbps in each direction (2000 Mbps total). The network adapter card features the Realtek RTL8111G chipset, which is designed to deliver the performance and enhanced capabilities you need for reliable network connections to your server or computer.

A versatile and cost-effective solution

This versatile quad-port network card is ideal for many business applications requiring upgrades to servers or workstations, adding feature-rich Gigabit networking with four independent ports. Compatible with a broad range of operating systems, this cost-effective PCIe Gigabit NIC is suitable for many SMB and Enterprise applications such as virtualized environments that require multiple NICs (check your VM software for chipset compatibility).

The ST1000SPEX43 is backed by a StarTech.com 2-year hardware warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Provides simultaneous access to multiple networks for desktop PC clients, servers, and workstations that have a limited number of PCI Express slots available
- Maximizes the number of RJ45 ports within a system or high-end workstations and servers
- Ideal for VM environments with multiple operating systems, requiring shared or dedicated NICs
- Provides redundant connectivity to ensure an uninterrupted network connection

Features

- Add four independent Gigabit RJ45 ports to connect to multiple networks for high-bandwidth workstations and servers
- Realtek RTL8111G chipset for reliable performance
- Supports full-duplex flow control
- Wake-on-LAN and remote wake-up support
- Fully compliant with IEEE 802.3, IEEE 802.3u, IEEE 802.3ab networks
- Supports autonegotiation with next-page capacity
- Crossover detection and auto-correction (Auto-MDIX)
- Up to 9K jumbo frame support
- Support for IEEE 802.1Q VLAN tagging and IEEE 802.1P layer 2 priority encoding
- Microsoft NDIS5 checksum offload (IP, TCP, UDP) and large send offload support

Hardware	Warranty	2 Years
	Bus Type	PCI Express
	Card Type	Standard Profile
	Chipset ID	Realtek - RTL8111G
	Industry Standards	Compliant with IEEE 802.3, IEEE 802.3u, IEEE 802.3ab
	Interface	RJ45 (Gigabit Ethernet)
	Ports	4
Performance	Auto MDIX	Yes
	Compatible Networks	10/100/1000 Mbps
	Full Duplex Support	Yes
	Jumbo Frame Support	9K max.
	Maximum Data Transfer Rate	2000Mbps (Full Duplex)
	Promiscuous Mode	Yes
Connector(s)	Connector Type(s)	1 - PCI Express x4 Male
	External Ports	4 - RJ-45 Female
Software	OS Compatibility	Windows® XP, 7, 8, 8.1, 10 Windows Server® 2003, 2012, 2016, 2019 Linux Kernel 2.4.x to 4.11.x <i>LTS Versions only</i>
Special Notes / Requirements	System and Cable Requirements	Available PCI Express x4 or higher (x8, x16) slot
Indicators	LED Indicators	4 - Link 4 - Activity
Environmental	Humidity	5% ~ 95% RH
	Operating Temperature	0°C to 55°C (32°F to 131°F)
	Storage Temperature	-40°C to 75°C (-40°F to 167°F)
Physical Characteristics	Color	Yellow
	Product Height	0.7 in [1.8 cm]
	Product Length	5.4 in [13.8 cm]
	Product Width	4.7 in [12 cm]
	Weight of Product	3.4 oz [95 g]
Packaging Information	Package Height	1.6 in [40 mm]

Package Length	5.7 in [14.5 cm]
Package Width	8.2 in [20.9 cm]
Shipping (Package) Weight	6.5 oz [184 g]

What's in the Box	Included in Package	1 - PCIe Gigabit network card - 4 port
--------------------------	---------------------	--

Product appearance and specifications are subject to change without notice.