

## 10-Port USB 3.0 Hub with Charge and Sync Ports - 2 x 1.5A Ports

Product ID: ST103008U2C



This 10-port USB 3.0 hub enhances your system's capabilities by providing fast-charging for mobile devices, plus quick access to your USB devices, making it perfect for business or home-office settings.

### Fast-charge your mobile devices

As a charging station, the hub features two easy-access 1.5 amp charge-and-sync ports, so you can easily fast-charge your smartphones, tablets and other mobile devices. Plus, you can still connect all of your vital peripherals to the remaining data ports. Because the hub supports USB Battery Charging Specification 1.2, you can charge most mobile devices, including Apple devices and Android™ devices such as the Samsung Galaxy™.

## **Increase your productivity with ten USB 3.0 ports**

Designed for maximum scalability, this 10-port hub boosts your productivity by putting all of your USB devices within easy reach. With USB 3.0 transfer rates up to 5Gbps, it supports high-bandwidth devices such as external hard drive enclosures, flash drives, high-resolution webcams, video cameras, and more.

## **Designed for easy use**

With its sleek and compact design, you can easily position the USB 3.0 (also known as USB 3.1 Gen 1) hub on your desk or workspace to make your USB devices more accessible. There's also ample space between the USB 3.0 ports, so it's easy to plug and unplug the devices you use the most.

The USB 3.0 hub is multi-platform compatible and is natively supported in virtually all operating systems including Windows® and Mac, which makes for an easy setup with no driver installation required.

The ST103008U2C is backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Conveniently fast-charge your mobile devices or sync with your computer
- Deploy as a charging station or data hub in hot-desk environments
- Upgrade the capabilities of your desktop or laptop with 10 additional USB 3.0 ports
- Make hard-to-reach USB ports more accessible

### Features

- Boost your system's capabilities and turn one USB 3.0 port into ten
- Fast-charge your smartphone or tablet, using two charge-and-sync ports with 1.5A output
- Charge a variety of mobile devices, including Apple and Samsung Galaxy devices, with support for USB Battery Charging Specification 1.2
- Includes a 48W universal power adapter
- Multi-platform compatibility, with no drivers required
- Slim and sleek black enclosure
- Built-in on/off power button
- SuperSpeed USB 3.0 throughput up to 5Gbps
- LED indicators for port status
- Supports plug-and-play, hot-swap, and hot-plugging
- Backward compatible with USB 2.0 and 1.x devices

<b>Hardware</b>	Warranty	2 Years
	Bus Type	USB 3.0
	Chipset ID	VIA/VLI - VL812
	Fast-Charge Port(s)	Yes
	Industry Standards	USB Battery Charging Specification Rev. 1.2 USB 3.0 - Backward compatible with USB 2.0/1.1
	Interface	USB 3.0
	Ports	10
	USB-C Device Port(s)	No
	USB-C Host Connection	No
<b>Performance</b>	Maximum Data Transfer Rate	5 Gbps
	Type and Rate	USB 3.0 - 5 Gbit/s
<b>Connector(s)</b>	Connector Type(s)	8 - USB Type-A (9 pin) USB 3.0 Female 2 - USB 3.0 A (Fast-Charge, 9 pin, SuperSpeed) Female
	OS Compatibility	OS Independent; No additional drivers or software required
<b>Special Notes / Requirements</b>	<b>Note</b>	If connected to a USB 2.0 host port, performance may be limited  <b>Charge and sync port(s) with a fast-charge icon:</b> If your host computer is turned off, in sleep mode, or disconnected, the hub will disable data sync mode and enable fast-charge mode automatically  If your host computer is turned on, a charge and sync port will provide a standard charge to a connected device plus simultaneous data sync capabilities
	System and Cable Requirements	Host computer with an available USB 3.0 port
<b>Indicators</b>	LED Indicators	10 - Port status (Blue)
<b>Power</b>	Center Tip Polarity	Positive
	Input Current	1.0 A
	Input Voltage	100 ~ 240 AC
	Output Current	4 A
	Output Voltage	12 DC
	Plug Type	N
	Power Consumption (In Watts)	48
	Power Source	AC Adapter Included

<b>Environmental</b>	Humidity	10% ~ 90% RH (Non-condensing)
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-10°C to 70°C (14°F to 158°F)
<b>Physical Characteristics</b>	Color	Black
	Enclosure Type	Plastic
	Form Factor	Desktop
	Product Height	0.9 in [24 mm]
	Product Length	7.9 in [201 mm]
	Product Weight	5.1 oz [144 g]
	Product Width	2.4 in [60 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	22.6 oz [639 g]
<b>What's in the Box</b>	Included in Package	1 - 10-port USB 3.0 hub with charge & sync ports
		1 - USB 3.0 host cable [80 cm/31.5 in.]
		1 - universal power adapter
		4 - universal power adapter (NA/JP, UK, EU, ANZ)

Product appearance and specifications are subject to change without notice.