

4K HDMI 2-Port Video Splitter – 1x2 HDMI Splitter – Powered by USB or Power Adapter – 4K 30Hz

Product ID: ST122HD4KU



The ST122HD4KU 2-port video splitter supports Ultra HD (4K) ensuring astonishing picture quality, four times the resolution of high-definition 1080p, while sharing a 4K HDMI video source between two HDMI displays.

The 4K splitter is backward compatible with previous HDMI revisions, supporting 1080p / 720p HDMI video resolution devices such as computers, Blu-ray players and cable TV set-top boxes. Even if you don't require 4K video today, the video splitter ensures you'll be ready to take advantage of tomorrow's display technology while still working with the devices you already have. Plus, this splitter supports 3D, enabling you to use the splitter with your stereoscopic 3D video source on active or passive 3D displays.

For a hassle-free setup you can power the HDMI splitter with the included USB cable, or power adapter depending on which is most convenient for you. Plus, the splitter features a built-in HDMI source cable, which lets you connect it directly to your HDMI source without the expense of additional cabling.

The ST122HD4KU is backed by a StarTech.com 2-year warranty, and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Display a 4K HDMI signal on two different HDMI displays
- Use to showcase 4K displays, by outputting the same video source on multiple displays
- Display corporate information or advertising on multiple displays at a shopping center
- Use to display a stock ticker or promotional information at financial institutions
- Present the same information on multiple displays in waiting rooms in healthcare facilities

Features

- Supports Ultra HD video resolutions up to 4K @ 30Hz
- USB-powered, includes optional power adapter
- Built-in HDMI source cable
- Supports 3D video
- Support for 7.1 surround sound audio
- 2x HDMI outputs
- Small footprint

Hardware	Warranty	2 Years
	Audio	Yes
	AV Input	HDMI
	AV Output	HDMI
	Industry Standards	HDMI 1.4
	Ports	2
Performance	Audio Specifications	7.1 Surround sound
	Maximum Digital Resolutions	4K @ 30 Hz
	Supported Resolutions	3840x2160 (4K) 2560x1600 1920x1200 1920x1080 (1080p) 1280x720 (720p)
	Wide Screen Supported	Yes
Connector(s)	Connector A	1 - HDMI (19 pin) Male
	Connector B	2 - HDMI (19 pin) Female
Power	Input Current	0.5 A
	Input Voltage	100 ~ 240 AC
	Output Current	2 A
	Output Voltage	5 DC
	Plug Type	N
	Power Consumption (In Watts)	10
	Power Source	AC Adapter Included
Physical Characteristics	Color	Black
	Product Height	0.7 in [18 mm]
	Product Length	24.2 in [615 mm]
	Product Weight	2.8 oz [78 g]
	Product Width	2.1 in [53 mm]
Packaging Information	Shipping (Package) Weight	14 oz [396 g]
What's in the Box	Included in Package	1 - HDMI splitter 1 - universal power adapter (NA/EU/UK/AU) 1 - USB power cable

1 - instruction manual

Product appearance and specifications are subject to change without notice.