

4 Port DVI Video Splitter with Audio

Product ID: ST124DVIA



The ST124DVIA DVI splitter lets you share one DVI video and audio source on four displays and acts as a signal amplifier that allows you to locate your DVI monitors up to 33ft (10 m) away from your computer or DVI signal source.

With support for high definition resolutions up to 1080p (HDTV)/1920x1200 (PC), the DVI splitter delivers a simple and convenient DVI video solution that suits virtually any application or operating environment (classroom, healthcare, professional A/V, control centres, retail POS environments).

The DVI video splitter/distribution amplifier is easy to install, providing you with flawless digital video that will help you get the most from your DVI-enabled monitors, projectors, or plasma screens.

This product is TAA compliant and backed by StarTech.com's 2-year warranty with FREE lifetime tech support.

Certifications, Reports and Compatibility



Applications

- Connect DVI projectors, monitors, large displays, and wall display systems for digital signage applications and ensuring content is delivered to target audience.
- Great for use in tradeshows, POS retail, healthcare, transportation terminals, education, house of worship.

Features

- Supports resolutions of up to 1920 x 1200 pixels @ 60 Hz
- Split both video and 3.5mm analog stereo audio
- DVI, and HDCP compliant for easier HD video distribution
- Easy setup for a quick connection in minutes
- Accurate and reliable reproduction of digital video signal, with no signal attenuation or distortion

Hardware	Warranty	2 Years
	AV Input	DVI
	AV Output	DVI
	Cabling	DVI
	Ports	4
Performance	Max Distance	10 m / 33 ft
	Maximum Digital Resolutions	1920x1200 @ 60Hz
	Wide Screen Supported	Yes
Connector(s)	Connector A	1 - 3.5 mm Mini-Jack (3 Position) Female 1 - DVI-I (29 pin) Female
	Connector B	4 - 3.5 mm Mini-Jack (3 Position) Female 4 - DVI-I (29 pin) Female
Indicators	LED Indicators	1 - Green - Power/Link 4 - Green - Link
Power	Center Tip Polarity	Positive
	Input Voltage	110V-240V AC
	Output Current	0.6A
	Output Voltage	9 DC
	Power Consumption (In Watts)	5.4
	Power Source	AC Adapter Included
Environmental	Humidity	0~80% RH
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Physical Characteristics	Color	Black
	Enclosure Type	Aluminum
	Product Height	1.7 in [44 mm]
	Product Length	8.7 in [220 mm]
	Product Weight	38.8 oz [1100 g]
	Product Width	5.3 in [135 mm]
Packaging Information	Shipping (Package) Weight	4.2 lb [1.9 kg]

What's in the Box	Included in Package
	1 - 4-port DVI splitter
	2 - rack mounts
	1 - screw kit
	4 - rubber feet
	1 - universal power adapter (US, UK, EU, ANZ)
	1 - instruction manual

Product appearance and specifications are subject to change without notice.