

3-Port Portable USB 3.0 Hub plus Gigabit Ethernet - Aluminum with Built-in Cable

Product ID: ST3300GU3B



The ST3300GU3B Portable USB 3.0 Hub is TAA compliant features an integrated GbE port, enabling you to expand your laptop connectivity by adding three external USB 3.0 ports, as well as a Gigabit network port via a single USB 3.0 connection. This hub is an ideal laptop accessory for your Microsoft Surface™ Pro 4, Surface Pro 3, Surface Book, Dell™ XPS 13, and many other devices.

The hub merges Gigabit network support and USB 3.0 hub access into lightweight yet sturdy aluminum casing, providing vital connectivity ports that are often limited or nonexistent on modern mobile computers, while remaining compact and travel-friendly. Plus, with an attached USB 3.0 host connection cable there's no need to carry a separate cable with you, so you can tuck the hub neatly into your laptop bag for maximum portability.

For faster and more consistent network connections, the integrated Ethernet port leverages the 5Gbps capabilities of the USB 3.0 interface to provide wired Gigabit access that is fully compatible with IEEE 802.3/u/ab standards. Plus, the GbE port supports Wake-on-LAN (WOL), so you can remotely wake your computer over your network.

An ideal laptop accessory, this mobile USB hub is great for connecting low-power peripherals like a mouse, keyboard or USB flash drive, and also includes a universal power adapter for connecting devices such as [external hard drive enclosures](#).

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Work from your Ultrabook, laptop or netbook easily while you're on the run or on the road, the perfect travel accessory with more connectivity options
- An ideal laptop accessory for Microsoft Surface Pro 4, Surface Pro 3, Surface Book, Dell XPS 13, Dell Latitude 11 5000 Series 2-in-1 and other devices
- Connect a wide variety of peripherals at home / office to a laptop, all from a single USB 3.0 connection
- Add Gigabit support to your laptop for use in boardrooms, hotels, classrooms, offices, or home environments
- Replace a failed built-in Ethernet port on a laptop, or upgrade to 1000 Mbps Gigabit connectivity

Features

- TAA Compliant
- Provides three USB 3.0 hub ports, with support for up to 5 Gbps
- Gigabit Ethernet port (RJ45) with Wake-on-LAN (WOL) support
- Aluminum casing with a compact, slim, and lightweight design for maximum portability
- Dongle-style combination adapter with built-in USB 3.0 cable
- IEEE 802.3, IEEE 802.3u, IEEE 802.3ab, IEEE 802.3az compatible
- Supports 10/100/1000 Mbps half and full-duplex operation
- Backward compatible with USB 2.0 and 1.x devices
- Universal Power Adapter (NA/UK/EU) included

Hardware	Warranty	2 Years
	Bus Type	USB 3.0
	Chipset ID	Genesys Logic - GL3522 ASIX - AX88179
	Fast-Charge Port(s)	No
	Industry Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3ab IEEE 802.3az Energy-Efficient Ethernet, IEEE 802.3x Flow Control, 802.1q VLAN Tagging, 802.1p Layer 2 Priority Encoding USB 3.0 - Backward compatible with USB 2.0 and 1.1
	Interface	USB 3.0 USB 3.1 Gen 1 RJ45 (Gigabit Ethernet)
	Ports	3
	USB-C Device Port(s)	No
	USB-C Host Connection	No
	Performance	Auto MDIX
Compatible Networks		10/100/1000 Mbps
Flow Control		Full duplex flow control
Full Duplex Support		Yes
Jumbo Frame Support		4K max.
Maximum Data Transfer Rate		5 Gbps (USB 3.0) 2 Gbps (Ethernet; Full-Duplex)
Type and Rate		USB 3.0 - 5 Gbit/s
Connector(s)	Connector Type(s)	3 - USB Type-A (9 pin) USB 3.0 Female 1 - RJ-45 Female 1 - USB Type-A (9 pin) USB 3.0 Male
	Software	OS Compatibility
		Windows® XP, Vista, 7, 8, 8.1, 10 Windows Server® 2003, 2008 R2, 2012, 2012 R2, 2016, 2019 Mac OS® 10.6 to 10.14 Chrome OS™ Linux 2.6.x to 4.11.x <i>LTS versions only</i>
Special Notes / Requirements	Note	If connected to a USB 2.0 host port, performance may be limited
	System and Cable Requirements	Available USB 3.0 port

Indicators	LED Indicators	1 - Link 1 - Activity
Power	Center Tip Polarity	Positive
	Input Current	300 mA
	Input Voltage	100 - 240 AC
	Output Current	2 A
	Output Voltage	5 DC
	Plug Type	H
	Power Consumption (In Watts)	10
	Power Source	AC Adapter Included
Environmental	Humidity	0~85% RH (Non-Condensing)
	Operating Temperature	0°C to 50°C (32°F to 122°F)
	Storage Temperature	-10°C to 75°C (14°F to 167°F)
Physical Characteristics	Cable Length	5.8 in [148 mm]
	Color	Black
	Enclosure Type	Aluminum
	Form Factor	Compact
	Product Height	0.6 in [1.4 cm]
	Product Length	3.4 in [87 mm]
	Product Width	1.7 in [43 mm]
	Weight of Product	2.2 oz [62 g]
Packaging Information	Package Height	2.1 in [53 mm]
	Package Length	6 in [15.2 cm]
	Package Quantity	1
	Package Width	8.5 in [21.7 cm]
	Shipping (Package) Weight	13.2 oz [374 g]
What's in the Box	Included in Package	1 - Aluminum USB 3.0 Hub w/ GbE Adapter 1 - Universal Power Adapter (NA/JP, EU, UK, ANZ) 1 - Driver CD 1 - Instruction Manual

Auto-Negotiation

Yes

Product appearance and specifications are subject to change without notice.