

## 6 Port USB 3.0 / USB 2.0 Combo Hub with 2A Charging Port – 2x USB 3.0 & 4x USB 2.0

Product ID: ST7320USBC



The ST7320USBC 6-Port USB 3.0/2.0 Combo Hub features a special high-output dedicated charging port which enables you to charge USB devices by providing up to 2A of power, or it can add 2x USB 3.0 and 4x USB 2.0 ports to a computer through a single USB 3.0 host connection.

The hub includes an external power adapter, which when connected enables charging some portable electronic devices (e.g. an iPhone® or other Smartphone), even without a USB connection to a host computer.

Offering a unique design that features USB ports along 3 sides of the hub, as well as a combination of USB 2.0 and 3.0 ports, this versatile and flexible USB hub is ideal for both laptop and desktop computers.

The ST7320USBC USB 3.0/2.0 hub is backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Add multiple USB 3.0 and USB 2.0 to a computer system to support more device connections
- Charge a Smartphone
- Charging high-powered portable devices (such as tablets) which require special high output USB ports for charging
- Make USB ports that are hard to access more accessible, by being positioning the hub in a convenient location (within cable reach)
- Extend the range of a USB device by having the hub act as a mid-point repeater

### Features

- 2x USB 3.0 and 4x USB 2.0 ports that can be all accessed simultaneously
- 2 Amp high output USB Dedicated Charging Port (DCP)
- Includes 20 watt power adapter and host USB 3.0 cable
- Universal, multi-platform compatible, with no additional drivers or software required
- SuperSpeed USB 3.0 compliant host interface, with support for up to 5 Gbps of data bandwidth

<b>Hardware</b>	Warranty	2 Years
	Chipset ID	VIA/VLI - VL813
	Fast-Charge Port(s)	Yes
	Interface	USB 3.0
	Ports	7
	USB-C Device Port(s)	No
	USB-C Host Connection	No
<b>Performance</b>	Type and Rate	USB 2.0 - 480 Mbit/s USB 3.0 - 4.8 Gbit/s
	<b>Connector(s)</b>	External Ports 1 - USB Type-B (9 pin) USB 3.0 Female 2 - USB Type-A (9 pin) USB 3.0 Female 4 - USB Type-A (4 pin) USB 2.0 Female
<b>Software</b>	OS Compatibility	OS Independent
<b>Special Notes / Requirements</b>	System and Cable Requirements	Available USB 3.0 or 2.0 port
<b>Indicators</b>	LED Indicators	1 - Power
<b>Power</b>	Input Current	0.6 A
	Input Voltage	110V-240V AC
	Output Current	4 A
	Output Voltage	5 DC
	Plug Type	H
	Power Consumption (In Watts)	20
	Power Source	AC Adapter Included
<b>Environmental</b>	Humidity	5~90% RH
	Operating Temperature	0°C to 85°C (32°F to 185°F)
	Storage Temperature	-10°C to 95°C (14°F to 203°F)
<b>Physical Characteristics</b>	Color	Black
	Enclosure Type	Plastic
	Form Factor	Desktop
	Product Height	0.8 in [20 mm]
	Product Length	3.9 in [99 mm]

	Product Weight	2.7 oz [75.4 g]
	Product Width	2.4 in [60 mm]
<b>Packaging Information</b>	Package Quantity	1
	Shipping (Package) Weight	17.6 oz [500 g]
<b>What's in the Box</b>	Included in Package	1 - 6 Port USB Hub
		1 - USB 3.0 Cable
		4 - Universal Power Adapter (NA/JP, EU, UK, ANZ)
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.