

Mobile Sit-Stand Workstation

Product ID: STSCART



Encourage interactive classrooms and engaged learning with StarTech.com mobile sit-stand workstations.

These sit-stand desks allow students to set up their learning environments to suit their needs. The workstations can easily be adjusted from a sitting position to a standing position with no disruptions to the class. Teachers can arrange and rearrange their classrooms according to their lessons, they can set up individual desks for tests or lectures, or group two or more desks together for projects. The two front casters can be locked in place to prevent the workstations from moving.

Simple height adjustments for individualized comfort

Moving between sitting and standing throughout the day brings many health benefits, from increased circulation to reduced fatigue. The sit-stand workstations make it easy for students to change their positioning throughout the day, keeping them attentive and focused. Giving students the freedom to stand when needed can also help to reduce anxiety and restlessness.

Students can adjust the desk to any height between 29.5" (750 mm) and 45" (1150 mm), they simply need to squeeze the lever located under the work surface, and then move the workstation up or down. The adjustment lever on the right side of the desktop can also be locked using the provided key, so that the height won't accidentally change if a student knocks the lever.

There are no preset heights, so each student can find the precise height they need to work most comfortably.

Large work surface sized to fit student needs

The large surface area of the desktop, 24" (600 mm) x 31.5" (800 mm), provides ample room for all schoolwork and supplies such as textbooks, pens, and other stationery.

For laptop configurations, the workstations feature cable clips that run down the column in order to help keep cables organized. The workstations can also be combined with [monitor mounts](#) to add displays. The work surface also provides enough room for a keyboard and mouse.

Note: If more than 10 lb. (4.5 kg) of weight is added to the work surface, some manual force will be needed to raise the desktop.

Mobile desks, perfect for customizable classrooms

Teachers can create dynamic environments to accommodate different needs. They simply need to unlock the two front casters and move the workstations around the classroom to:

- Split students into groups for projects
- Pull individuals aside for personalized one-on-one learning
- Sit the students in a circle for presentations and to encourage group conversations
- Set up a standard classroom configuration for lectures and tests

Teachers can also use the workstations for presentation purposes. The mobile workstations are ideal for moving around from class to class with laptops and other tools, and the height can be adjusted and locked.

The portable desks can also be used in the following settings:

- Office training rooms
- Warehouses and manufacturing sites where workstations are shared amongst many individuals and need to be moved between different testing areas
- Home offices
- IT departments as server crash carts

The STSCART is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Create sit-to-stand workstations with versatile applications in schools, business settings, corporate and institutional environments, or home offices
- Add flexibility to the classroom or work environment with mobile workstations

Features

- Increase students' comfort by allowing them to change their position from sitting to standing
- Height adjustment lever with locking mechanism
- Provide enough room for all supplies such as textbooks, pens and tools with a 24" x 31.5" work surface
- Customize classrooms to create dynamic learning environments
- Compatible with StarTech.com dual and single monitor arms: ARMPIVOTE, ARMPIVOT, and ARMSLIM (sold separately)
- Locking casters
- Height range adjustments: 29.5" (750 mm) to 45" (1150 mm)
- Lift capacity: 10 lb. (4.5 kg)
- Static load capacity: 110 lb. (50 kg)
- Cable clips for cable management

Hardware	Warranty	2 Years
	# of Displays Supported	1
	Cable Management	Yes
	Casters	Included
	Orientation	Vertical
Performance	General Specifications	Lift Capacity 10 lb [4.5 kg] Static Load Capacity 110 lb [50 kg]
	Height Adjustment	Yes
	Maximum Height	45.3 in [1150 mm]
	Minimum Height	29.5 in [750 mm]
Special Notes / Requirements	Note	If more than 10 lb. (4.5 kg) of weight is added to the desktop surface, some manual force will be needed to raise the desktop.
Physical Characteristics	Color	Black & Silver
	Product Height	45.3 in [115 cm]
	Product Length	23.6 in [60 cm]
	Product Width	31.5 in [80 cm]
	Weight of Product	53 lb [24 kg]
Packaging Information	Package Height	6.7 in [17 cm]
	Package Length	33.1 in [84 cm]
	Package Width	25.2 in [64 cm]
	Shipping (Package) Weight	60.8 lb [27.5 kg]
What's in the Box	Included in Package	1 - base 2 - casters 2 - locking casters 1 - column 1 - desktop 4 - covers 8 - M6x15 mm socket-head screws 12 - M6x15 mm flat-head screws 1 - M5 hex key 1 - M4 hex key

4 - cable clips

1 - key

1 - instruction manual

Product appearance and specifications are subject to change without notice.