

16 Port 1U Rackmount USB PS/2 KVM Switch with OSD

Product ID: SV1631DUSBGB



The SV1631DUSBGB 16 Port 1U Rack Mount USB PS/2 KVM Switch with OSD offers a dependable computer management tool that allows you to control up to 16 USB or PS/2 connected computers from a single keyboard, mouse and monitor.

The KVM switch offers maximum control, allowing you to switch computers using hotkey commands or front panel push-buttons, and offers the added convenience of an On Screen Display to quickly access configuration options.

A suitable addition to server room operations, the 16 port switch can be rack-mounted into 1U of cabinet space, and can be cascaded with multiple KVM switches to deliver control of up to 136 computers from this single switch.

This high quality USB PS/2 KVM Switch is TAA compliant and backed by a StarTech.com 3-year warranty with free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Add single console administration to your Co-location/ISP facility saving you time and money
- Create a scalable, streamlined access solution in your Datacenter or Server Farm
- Perfect for manufacturing line computer control, simplifying access to multiple systems
- Great for PC test/burn-in computer control saving the desk space required for multiple monitors, keyboards and mice

Features

- Connect USB and PS/2 based computer systems
- OS independent – No software or drivers required
- Auto-scan function cycles through computers sequentially
- Cascade configuration expands system capability
- Front panel push-buttons and Hot-key functions allow for easy switching
- On Screen Display (OSD) supports naming connected computers
- USB & PS2 console interfaces for keyboard and mouse
- OSD security option allows selected PCs to be password protected from unauthorized use
- Rugged, all-metal 1U chassis for use in harsh environments and space-saving cabinets

Hardware	Warranty	3 Years
	Audio	No
	Cables Included	No
	Daisy-Chain	Yes
	KVM Ports	16
	Number of Monitors Supported	1
	PC Interface	USB and PS/2
	PC Video Type	VGA
	Rack-Mountable	Yes
Performance	Hot-Key Selection	Yes
	IP Control	No
	Maximum Analog Resolutions	1920 x 1440 @60hz
	Maximum Cascaded Computers	136
	Maximum Number of Users	1
	On-Screen Display	No
	Port Selection Support	Push Button and Hotkeys
Software	OS Compatibility	OS independent; No software or drivers required
Power	Center Tip Polarity	Positive
	Input Current	0.2 A
	Input Voltage	100 ~ 240 AC
	Output Current	0.6 A
	Output Voltage	9 DC
	Plug Type	M
	Power Consumption (In Watts)	5.4
	Power Source	AC Adapter Included
Environmental	Operating Temperature	5°C to 40°C (41°F to 104°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Physical Characteristics	Enclosure Type	Steel
	Product Height	45 mm [1.8 in]
	Product Length	438 mm [17.2 in]
	Product Weight	3100 g [109.4 oz]

	Product Width	180 mm [7.1 in]
Packaging Information	Shipping (Package) Weight	3.8 kg [8.4 lb]
What's in the Box	Included in Package	1 - 16 Port KVM Switch 2 - Mounting Brackets 1 - PS/2 keyboard and mouse Y cable 1 - Power Adapter 4 - foot pads 1 - User Manual

Product appearance and specifications are subject to change without notice.