

2 Port USB DisplayPort Cable KVM Switch w/ Audio and Remote Switch - USB Powered

Product ID: SV211DPUA



The SV211DPUA 2-Port DisplayPort® Cable KVM Switch with Audio and Remote Switching Control lets you control two DisplayPort, USB equipped PCs with a single monitor, keyboard, mouse and audio peripheral set.

To help organize your desk without sacrificing work space, this compact DisplayPort USB KVM features integrated cables that can be connected directly to your system, while leaving a minimal footprint. The switch features a remote push-button on a 1.5 meter (5ft) integrated cable that can be placed in an easily accessible location, as well as keyboard hot-keys, and PC or Mac® compatible software for switching between systems. To eliminate the need for a bulky external power adapter and wall outlet, the DisplayPort KVM switch is USB-powered.

This KVM with DisplayPort video capability offers support for resolutions up to 2560x1600 for the ability to drive a large DisplayPort display for applications that require high graphical output.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Great for PC test/burn-in computer control, saving the desk space required for two monitors, keyboards and mice
- Perfect for sharing computers and attached peripherals in the home or home office
- Dual system control for single user workstations increasing user productivity in the office

Features

- Supports resolutions up to 2560x1600
- Switch PCs via push-button, hot-keys or switching software
- Space-saving design, minimal footprint
- Integrated KVM cables and remote switch
- Switching software supports PC and Mac® platforms
- USB Powered - No external power adapter required
- Independent audio/mic switching for uninterrupted audio
- Analog (3.5mm) and DisplayPort audio supported
- Supports hot-plugging
- Remote switch on 1.5m (5ft.) cable

Hardware	Warranty	2 Years
	Audio	Yes
	Cables Included	Yes
	Daisy-Chain	No
	KVM Ports	2
	Number of Monitors Supported	1
	PC Interface	USB
	PC Video Type	DisplayPort
	Rack-Mountable	No
Performance	Audio Specifications	Analog (3.5mm) and DisplayPort audio supported
	Hot-Key Selection	Yes
	IP Control	No
	On-Screen Display	No
	Port Selection Support	Push Button, Hotkeys, and Software
Connector(s)	Console Interface(s)	1 - DisplayPort (20 pin) Female 2 - 3.5 mm Mini-Jack (3 Position) 2 - USB Type-A (4 pin) USB 2.0
	Host Connectors	1 - DisplayPort (20 pin) Latching Male 1 - USB Type-A (4 pin) USB 2.0 Male 2 - 3.5 mm Mini-Jack (3 Position) Male
Software	OS Compatibility	Windows® 2000, XP, Vista, 7, 8, 8.1, 10 Windows Server® 2003, 2008 R2, 2012, 2016, 2019 Mac OS 10.6 to 10.9
Special Notes / Requirements	Note	OS Compatibility refers to KVM software only - the KVM itself can be used without software on any platform If you intend to convert the DisplayPort KVM to work with different video sources or displays such as HDMI or VGA, active adapters are required
Indicators	LED Indicators	1 - PC Selection indicator
Power	Power Source	USB-Powered
Environmental	Humidity	0~90% RH Non-Condensing
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-20°C to 60°C (4°F to 140°F)

Physical Characteristics	Cable Length	33.5 in [850 mm]
	Color	Black
	Enclosure Type	Plastic
	Product Height	0.9 in [2.3 cm]
	Product Length	3.5 in [88 mm]
	Product Width	2.6 in [66 mm]
	Weight of Product	13 oz [367 g]
Packaging Information	Package Height	2.4 in [62 mm]
	Package Length	9.8 in [25 cm]
	Package Width	6.4 in [16.3 cm]
	Shipping (Package) Weight	16.9 oz [480 g]
What's in the Box	Included in Package	1 - KVM Switch 1 - Software CD 1 - Instruction Manual

Product appearance and specifications are subject to change without notice.