

2 Port USB DVI KVM Switch Kit with Cables USB 2.0 Hub & Audio

Product ID: SV211KDVIEU



The SV211KDVIEU 2 Port USB DVI KVM Switch Kit with Cables, USB 2.0 Hub & Audio provides control of 2 DVI-enabled, USB-controlled computers, as well as independent audio/microphone switching for uninterrupted audio when switching between PCs.

This USB+DVI KVM Switch features support for high-resolution digital (1920x1200) and analog (2048x1536) video, plus an integrated USB 2.0 hub that enables you to share 2 high-speed USB devices between computers.

Compatible with Mac®, Linux and Windows® based computers, this compact DVI KVM is a great space-saving solution for a broad range of environments including SOHO (Small or Home Offices), gaming, multimedia production and more.

A complete, out-of-the-box solution, this DVI KVM Switch includes two 4 ft. DVI/Audio & Mic combo cables that simplify computer connection to the switch and help to eliminate cable clutter.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Ideal for conserving space when working with multiple desktops, workstations and servers
- Home/SOHO/multimedia environment dual system control for single user workstations
- Ideal for graphic designers, engineers, multi-media designers, and industries using CAD/CAM applications, where high resolution display units are required
- Applicable for call centers, help desks, education environments, home gamers, and PC enthusiasts

Features

- Supports resolutions up to 1920x1200(digital) and 2048x1536(analog)
- Integrated USB 2.0 hub allows you to share up to two high-speed USB devices between computers
- Compatible with all USB supported Operating Systems
- Compact design saves space
- Computer selection by push button, keyboard hotkeys and Switching Software (for Windows/Mac)
- Hot Pluggable - add or remove computers without having to power down
- LED indicators for easy status monitoring
- USB 2.0/1.1 specification compliant
- HDCP Compliant

Hardware	Warranty	2 Years
	Audio	Yes
	Cables Included	Yes
	Daisy-Chain	No
	KVM Ports	2
	Number of Monitors Supported	1
	PC Interface	USB
	PC Video Type	DVI
	Rack-Mountable	No
Performance	DVI Support	Yes
	Hot-Key Selection	Yes
	IP Control	No
	Maximum Analog Resolutions	2048x1536
	Maximum Digital Resolutions	1920x1200
	Maximum Number of Users	1
	On-Screen Display	No
	Port Selection Support	Push Button and Hotkeys
Connector(s)	Console Interface(s)	1 - DVI-I (29 pin) Female 2 - 3.5 mm Mini-Jack (3 Position) Female 2 - USB Type-A (4 pin) USB 2.0 Female
	Host Connectors	2 - DVI-I (29 pin) Female 2 - USB B (4 pin) Female
Software	OS Compatibility	OS independent; No software or drivers required
Indicators	LED Indicators	1 - Power/Computer Selection Indicator
Power	Center Tip Polarity	Positive
	Input Current	0.4A
	Input Voltage	110V-240V AC
	Output Current	2A
	Output Voltage	5 DC
	Plug Type	N
	Power Consumption (In Watts)	10
	Power Source	AC Adapter Included

Environmental	Humidity	0~90% RH
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Physical Characteristics	Color	White
	Enclosure Type	Plastic
	Product Depth	65 mm [2.6 in]
	Product Height	27 mm [1.1 in]
	Product Length	154 mm [6.1 in]
	Product Weight	160 g [5.6 oz]
	Product Width	155 mm [6.1 in]
Packaging Information	Shipping (Package) Weight	1.3 kg [2.8 lb]
What's in the Box	Included in Package	1 - 2 Port KVM
		2 - 4 ft. DVI/Audio&Mic combo cables
		2 - 4 ft. USB cables
		1 - Power Adapter
		1 - Software CD
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.