

2 Port High Resolution USB DVI Dual Link KVM Switch with Audio

Product ID: SV231DVIUAHR



The SV231DVIUAHR 2-Port High Resolution Dual-Link DVI USB KVM Switch provides simple, yet comprehensive control of 2 directly-connected computers, as well as audio switching capability and support for high resolution applications (supports resolutions beyond 1080p: 2560x1600 @ 60Hz, up to 3840 x 2400 at lower refresh rates), offering a superior KVM switching solution that integrates perfectly into demanding imaging, medical, and multimedia environments.

This 2-port DVI USB KVM Switch is compatible with all USB-supported operating systems, and features a built-in USB 2.0 hub that allows you to share additional (up to 2) high speed USB devices between computers.

This product is TAA compliant and backed by a Startech.com 3-year warranty with free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Designed for large and high resolution displays such as Multimedia Displays, Stock trading setups, and Medical Screens
- Ideal for using desktops, workstations and servers with Ultra High resolution displays
- Great for television and graphic production studios where crisp, loss-less digital images are crucial
- Sharing high-end gaming computers and USB devices in the home

Features

- Designed for high-resolution applications: 2560x1600 @ 60Hz: Higher resolutions (3840 x 2400) are supported at lower refresh rates
- Hot-key or front panel push-button computer selection
- Integrated USB 2.0 hub allows you to share up to three high-speed USB devices between computers
- All metal chassis for long-term durability
- Compatible with all USB-supported Operating Systems
- HDCP Compliant

Hardware	Warranty	3 Years	
	Audio	Yes	
	Cables Included	No	
	Daisy-Chain	No	
	KVM Ports	2	
	Number of Monitors Supported	1	
	PC Interface	USB	
	PC Video Type	DVI	
	Rack-Mountable	No	
Performance	DVI Support	Yes	
	Hot-Key Selection	Yes	
	IP Control	No	
	Maximum Digital Resolutions	2560x1600 @ 60Hz	
	Maximum Number of Users	1	
	On-Screen Display	No	
	Port Selection Support	Push Button and Hotkeys	
Connector(s)	Console Interface(s)	1 - DVI-I (29 pin) Female 1 - USB Type-A (4 pin) USB 2.0 Female 2 - 3.5 mm Mini-Jack (3 Position) Female	
	Host Connectors	2 - DVI-I (29 pin) Female 2 - USB B (4 pin) Female 4 - 3.5 mm Mini-Jack (3 Position) Female	
	Software	OS Compatibility	OS independent; No software or drivers required
	Special Notes / Requirements	Note	Resolutions exceeding 2560x1600 can be obtained by using a lower refresh rate. Example 3840x2400 @30Hz
Power	Center Tip Polarity	Positive	
	Input Current	0.8A	
	Input Voltage	110V-240V AC	
	Output Current	1.5A	
	Output Voltage	12 DC	
	Plug Type	M	
	Power Consumption (In Watts)	18	

	Power Source	AC Adapter Included
Environmental	Humidity	0~80% RH
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Physical Characteristics	Color	Black
	Enclosure Type	Steel
	Product Height	1.6 in [40 mm]
	Product Length	6.3 in [159 mm]
	Product Weight	22.6 oz [640 g]
	Product Width	3.9 in [100 mm]
Packaging Information	Shipping (Package) Weight	2.5 lb [1.1 kg]
What's in the Box	Included in Package	1 - 2 Port DVI USB KVM
		1 - Rubber Foot Pad
		1 - Universal power adapter: comes ready for NA/EU/UK only when you buy in NA/EU/UK; comes ready for Australia and New Zealand only when you buy in Australia and New Zealand
		1 - User Manual

Product appearance and specifications are subject to change without notice.