

## 2 Port Professional USB KVM Switch Kit with Cables

Product ID: SV231USB



The SV231SUB 2 Port Professional USB KVM Switch Kit with Cables offers simple control of two Mac or PC computers from a single monitor/display and USB peripheral set (keyboard, mouse).

The 2 Port KVM switch includes 2 USB KVM cables, providing a complete out-of-the-box KVM solution saving you time and money. An integrated 3 port USB hub allows you to share connected USB peripherals between connected computers as though they were connected directly. A compact form factor design and rear-port connections to master and slave computers minimizes disruption to your workspace.

A cross-platform solution, this OS independent KVM switch supports high resolution applications up to 1920x1440, and provides a smooth operating experience when controlling mixed (Windows/Mac/Linux) environments.

This product is TAA compliant and backed by a Startech.com 3-year warranty with free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Dual system control for a single workstations increasing user productivity in the office
- Provide centralized control for multiple high-res Digital Signage server control
- Great for manufacturing line computer control, simplifying access to multiple systems
- Perfect for PC test/burn-in computer control saving the desk space required for two monitors, keyboards and mice

### Features

- Control 2 computers from one USB keyboard/mouse/monitor
- Share 3 different USB peripherals using the integrated hub
- High 1920x1440 resolution capability
- Front panel push buttons for easy computer selection
- OS independent - No software or drivers required
- Supports keyboard and mouse plug and play
- Selectable auto scan time interval
- Supports DDC2B VGA monitors
- USB self-power operation

|                                     |                              |  |
|-------------------------------------|------------------------------|--|
| <b>Hardware</b>                     | Warranty                     | 3 Years  |
|                                     | Audio                        | No   |
|                                     | Cables Included              | Yes  |
|                                     | Daisy-Chain                  | No   |
|                                     | KVM Ports                    | 2  |
|                                     | Number of Monitors Supported | 1  |
|                                     | PC Interface                 | USB  |
|                                     | PC Video Type                | VGA  |
|                                     | Rack-Mountable               | No   |
|                                     | U Height                     | 1U   |
| <b>Performance</b>                  | Auto Scan                    | 3, 8, 15 & 30 seconds  |
|                                     | DVI Support                  | No   |
|                                     | Hot-Key Selection            | No   |
|                                     | IP Control                   | No   |
|                                     | Maximum Analog Resolutions   | 1920 x 1440  |
|                                     | Maximum Cable Length         | 15 ft [4.6 m]  |
|                                     | Maximum Number of Users      | 1  |
|                                     | MTBF                         | 111,000 Hours  |
|                                     | On-Screen Display            | No   |
|                                     | Port Selection Support       | Push Button  |
| <b>Connector(s)</b>                 | Console Interface(s)         | 1 - VGA (15 pin, High Density D-Sub) Female<br>3 - USB Type-A (4 pin) USB 2.0 Female                                       |
|                                     | Host Connectors              | 2 - USB B (4 pin) Female<br>2 - VGA (15 pin, High Density D-Sub) Male  |
| <b>Software</b>                     | OS Compatibility             | OS independent; No software or drivers required  |
| <b>Special Notes / Requirements</b> | <b>Note</b>                  | This KVM supports the use of VGA cables up to 100ft in length - active extension required for USB to achieve that distance |
| <b>Power</b>                        | Center Tip Polarity          | Positive   |
|                                     | Input Current                | 0.4A   |
|                                     | Input Voltage                | 110V-240V AC   |
|                                     | Output Current               | 2A   |

|                                 |                              |                           |
|---------------------------------|------------------------------|---------------------------|
|                                 | Output Voltage               | 5 DC                      |
|                                 | Plug Type                    | N                         |
|                                 | Power Consumption (In Watts) | 10                        |
|                                 | Power Source                 | AC Adapter Included       |
| <b>Physical Characteristics</b> | Cable Length                 | 6 ft [1.8 m]              |
|                                 | Color                        | Black                     |
|                                 | Enclosure Type               | Steel                     |
|                                 | Product Height               | 1.6 in [40 mm]            |
|                                 | Product Length               | 4.9 in [124 mm]           |
|                                 | Product Weight               | 14.9 oz [421 g]           |
|                                 | Product Width                | 2.8 in [70 mm]            |
| <b>Packaging Information</b>    | Shipping (Package) Weight    | 2.5 lb [1.1 kg]           |
| <b>What's in the Box</b>        | Included in Package          | 1 - 2 Port USB KVM Switch |
|                                 |                              | 2 - 2 IN 1 USB/VGA Cables |
|                                 |                              | 1 - Power Adapter         |
|                                 |                              | 1 - Manual                |

Product appearance and specifications are subject to change without notice.