

2 Port Professional USB KVM Switch Kit with Cables

Product ID: SV231USBGB



The SV231SUBGB 2 Port Professional USB KVM Switch Kit with Cables offers simple control of 2 computers from a single monitor/display and USB peripheral set (keyboard, mouse).

The 2 Port KVM includes 2 USB KVM cables, for a complete out-of-the-box solution saving you time and money. An integrated 3 port USB hub allows you to share USB peripherals between computers as though they were connected directly. A compact form factor and rear-port connections minimizes disruption to your workspace.

This OS independent KVM supports resolutions up to 1920x1440, and provides a smooth operating experience in mixed (Windows/Mac/Linux) environments.

This product is TAA compliant and backed by a Startech.com 3-year warranty with free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Dual system control for a single workstations increasing user productivity in the office
- Provide centralized control for multiple high-res Digital Signage server control
- Great for manufacturing line computer control, simplifying access to multiple systems
- Perfect for PC test/burn-in computer control saving the desk space required for two monitors, keyboards and mice

Features

- Control 2 computers from one USB keyboard/mouse/monitor
- Share 3 different USB peripherals using the integrated hub
- High 1920x1440 resolution capability
- Front panel push buttons for easy computer selection
- OS independent - No software or drivers required
- Supports keyboard and mouse plug and play
- Selectable auto scan time interval
- Supports DDC2B VGA monitors
- Universal Power Adapter with EU and UK prong types included

Hardware	Warranty	3 Years
	Audio	No
	Cables Included	Yes
	Daisy-Chain	No
	KVM Ports	2
	Number of Monitors Supported	1
	PC Interface	USB
	PC Video Type	VGA
	Rack-Mountable	No
	U Height	1U
Performance	Auto Scan	3, 8, 15 & 30 seconds
	DVI Support	No
	Hot-Key Selection	No
	IP Control	No
	Maximum Analog Resolutions	1920x1440
	Maximum Cable Length	5 m [16.4 ft]
	Maximum Number of Users	1
	On-Screen Display	No
	Port Selection Support	Push Button
Connector(s)	Console Interface(s)	1 - VGA (15 pin, High Density D-Sub) Female 3 - USB Type-A (4 pin) USB 2.0 Female
	Host Connectors	2 - USB B (4 pin) Female 2 - VGA (15 pin, High Density D-Sub) Male
Software	OS Compatibility	OS independent; No software or drivers required
Power	Center Tip Polarity	Positive
	Input Current	0.4A
	Input Voltage	110V-240V AC
	Output Current	2A
	Output Voltage	5 DC
	Plug Type	N
	Power Consumption (In Watts)	10
	Power Source	AC Adapter Included

Physical Characteristics	Color	Black
	Enclosure Type	Steel
	Product Depth	70 mm [2.8 in]
	Product Height	40 mm [1.6 in]
	Product Weight	420 g [14.8 oz]
	Product Width	124 mm [4.9 in]
Packaging Information	Shipping (Package) Weight	1.5 kg [3.3 lb]
What's in the Box	Included in Package	1 - 2 Port KVM Switch
		2 - 6ft(1.83m) KVM Cables
		1 - Universal power adapter (EU/UK)
		1 - User Manual

Product appearance and specifications are subject to change without notice.