

4 Port Black USB KVM Switch Kit with Cables and Audio

Product ID: SV411KUSB



The SV411KUSB 4 Port USB KVM Switch Kit with Audio and Cables lets you control up to four USB-enabled computers using a single keyboard, mouse and VGA monitor and offers both hotkey and top panel push-button operation for simple switching between connected computers.

Designed to integrate seamlessly into any environment, the USB KVM switch offers a small footprint design (roughly the size of a deck of playing cards) and draws power from the connected computers, so it doesn't require an external power supply.

A suitable solution for virtually any application, the USB KVM switch supports video resolutions of up to 2048 x 1536 as well as audio switching. The USB KVM switch includes four, 4ft 4-in-1 VGA and USB Host Cables, providing everything needed for quick installation to provide a complete, out-of-the-box KVM solution.

Delivering dependable and convenient control of multiple computers from a single peripheral station, the KVM switch is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Control 4 USB-enabled computers using a single keyboard, mouse, and VGA monitor
- Applicable for call centers, help desks, education environments, home gamers, video editing, and PC enthusiasts
- Great for PC test/burn-in computer control saving the desk space required for multiple monitors, keyboards and mice
- Multiple system control for single user workstations, increasing user productivity in the office

Features

- Cables (4 ft.) included
- Includes audio support for a complete switching solution
- Maximum resolution: 2048 x 1536
- Switching type: Hotkey, push-button

| | | |
|---------------------------------|------------------------------|--|
| Hardware | Warranty | 2 Years |
| | Audio | Yes |
| | Cables Included | Yes |
| | Daisy-Chain | No |
| | KVM Ports | 4 |
| | Number of Monitors Supported | 1 |
| | PC Interface | USB |
| | PC Video Type | VGA |
| | Rack-Mountable | No |
| Performance | DVI Support | No |
| | Hot-Key Selection | Yes |
| | IP Control | No |
| | Maximum Analog Resolutions | 2048 x 1536 pixels |
| | Maximum Number of Users | 1 |
| | On-Screen Display | No |
| | Port Selection Support | Push Button and Hotkeys |
| Connector(s) | Console Interface(s) | 1 - VGA (15 pin, High Density D-Sub) Female 2 - 3.5 mm Mini-Jack (3 Position) Female 2 - USB Type-A (4 pin) USB 2.0 Female |
| | Host Connectors | 4 - VGA (15 pin, High Density D-Sub) Female 8 - 3.5 mm Mini-Jack (3 Position) Female |
| Software | OS Compatibility | OS independent; No software or drivers required |
| Power | Power Source | USB-Powered |
| Physical Characteristics | Cable Length | 4 ft [1.2 m] |
| | Color | Black |
| | Enclosure Type | Plastic |
| | Product Depth | 2.4 in [61 mm] |
| | Product Height | 1 in [25 mm] |
| | Product Weight | 6.7 oz [189 g] |
| | Product Width | 3.7 in [95 mm] |

| | | |
|------------------------------|---------------------------|--|
| Packaging Information | Shipping (Package) Weight | 3.1 lb [1.4 kg] |
| What's in the Box | Included in Package | 1 - 4 Port KVM Switch 4 - 4ft. Audio Cable (3.5mm speaker/mic) 4 - 4ft. VGA USB KVM Cable 1 - Driver CD 1 - Instruction Manual |

Product appearance and specifications are subject to change without notice.