

4 Port HDMI KVM Switch - 4K 30Hz - Dual Display

Product ID: SV431DHD4KU



This 4-port HDMI KVM switch lets you control four HDMI computers with a single mouse, keyboard and monitor up to 4K 30Hz. The KVM also features 3.5 mm audio and a built-in 2-port USB 3.0 hub.

4K at 30Hz UHD dual display

With support for ultra-high-definition 4K 30Hz resolutions, this 4-port KVM switch can drive dual HDMI displays with crystal clarity, making it ideal for graphical applications that require UHD capability.

Convenient and cost-effective USB 3.0 peripheral sharing

This 4-port KVM switch offers two USB 3.0 ports, as well as four HID keyboard and mouse ports, so you can share peripheral devices between each computer and avoid the cost of separate equipment. The USB 3.0 hub automatically switches your connected devices to the selected computer, saving you the hassle of disconnecting and reconnecting peripherals.

Complete multimedia capability

Along with dual UHD video capability, this KVM switch features auxiliary 3.5 mm dual-channel bi-directional audio ports. This independent analog audio lets you share your analog audio devices such as speakers or a microphone between each of your connected computers, giving you complete multimedia control of your systems.

The SV431DHD4KU is TAA compliant and backed by a StarTech.com 2-year warranty with free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Ideal for applications that require two displays at high resolutions such as graphic design, medical imaging, digital signage, multimedia design across four computers
- Great for those who need to share high-speed storage between up to four systems
- Perfect for creative professional applications such as video and sound design or editing

Features

- High-definition video quality with support for dual 4K at 30Hz displays
- Two built-in USB 3.0 ports and independent HID keyboard/mouse ports
- No software or drivers required
- Separate 3.5 mm auxiliary support
- Supports push-button and hotkey switching

Hardware	Warranty	2 Years	
	Audio	Yes	
	KVM Ports	4	
	Number of Monitors Supported	2	
	PC Interface	USB	
	PC Video Type	HDMI	
	Rack-Mountable	Yes	
Performance	Auto Scan	3, 8, 15 & 30 seconds	
	Hot-Key Selection	Yes	
	IP Control	No	
	Maximum Data Transfer Rate	5Gbps	
	Maximum Digital Resolutions	3840 x2160 @ 30Hz	
	Port Selection Support	Push Button and Hotkeys	
	Wide Screen Supported	Yes	
Connector(s)	Console Interface(s)	2 - HDMI 4 - USB Type-A (4 pin; HID Port) USB 1.1 2 - USB 3.1 USB Type-A (9 pin, Gen 1, 5 Gbps) 1 - 3.5mm Stereo Female 3 pos	
	Host Connectors	8 - HDMI 4 - USB 3.1 USB Type-B (9 pin, Gen 1, 5 Gbps) 4 - 3.5mm Stereo Female 3 pos	
	LED Indicators	4 - LED for Source Status and Selected PC 1 - power LED	
	Power	Center Tip Polarity	Positive
		Input Current	0.6 A
		Input Voltage	100 ~ 240 AC
Output Current		1.5 A	
Output Voltage		12 DC	
Plug Type		M	
Power Consumption (In Watts)		18W	
Power Source		AC Adapter Included	
Environmental	Humidity	0%~80%	

	Operating Temperature	0°C~40°C
	Storage Temperature	-10°C~60°C
Physical Characteristics	Color	Black
	Enclosure Type	Steel
	Product Height	2.5 in [63 mm]
	Product Length	8.7 in [220 mm]
	Product Weight	2.7 lb [1.2 kg]
	Product Width	5.1 in [130 mm]
Packaging Information	Shipping (Package) Weight	4 lb [1.8 kg]
What's in the Box	Included in Package	1 - KVM Switch
		1 - quick-start guide
		4 - rubber feet
		1 - universal power adapter (NA/JP, UK, EU, ANZ)

Product appearance and specifications are subject to change without notice.