

4-port KVM Switch with Dual VGA - USB 2.0

Product ID: SV431DVGAU2A



This USB KVM lets you connect four computers, each with dual VGA outputs, to a dual-monitor workstation. You can switch the workstation between each computer, as well as two additional USB peripheral devices and 3.5mm speakers & microphone.

Maximize productivity with dual video

With support for two VGA video inputs and four different computers, this KVM switch maximizes productivity. Not only can you access multiple computers, but you can also use two VGA monitors on each computer streaming independent content to each display, which gives you the freedom to multitask and increase your productivity. The VGA ports support resolutions up to 1920x1200 for maximum screen viewing space.

Multi-system access

Featuring dual video and support for your keyboard and mouse, along with a 2-port USB hub for additional peripheral devices, this KVM switch is perfect for accessing four separate systems using the same workstation. Support for your workstation plus two additional peripheral devices makes this KVM ideal for server control, simplifying access to multiple computer systems.

Hassle-free operation

This 4-port KVM ensures effortless operation with intuitive hotkey control. It provides a simple yet comprehensive solution for switching between each connected computer and also supports manual operation using the easy-to-access buttons located on the front of the switch.

The SV431DVG2A is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Rackmount your KVM switch

If you'd like to mount this KVM switch to your server rack, StarTech.com offers a [1U Rackmount Bracket](#) (sold separately) that turns this KVM into a rackmountable KVM.

Certifications, Reports and Compatibility



Applications

- Control four computers, each with dual head video cards, to increase your productivity at the office
- Work with multimedia applications such as video & photo editing
- Operate multiple computers in manufacturing lines
- Install in your server room, for multi-computer access

Features

- Maximum productivity with dual display and multi-computer access
- Hassle-free operation with hotkey and push-button switching
- Share your USB peripheral devices with built-in 2-port USB hub
- Supports resolutions up to 1920x1200
- 3.5mm speaker and microphone console support

Hardware	Warranty	2 Years		
	Audio	Yes		
	Cables Included	No		
	Daisy-Chain	No		
	KVM Ports	4		
	Number of Monitors Supported	2		
	PC Interface	USB		
	PC Video Type	VGA		
	Rack-Mountable	Optional		
Performance	DVI Support	No		
	Hot-Key Selection	Yes		
	IP Control	No		
	Maximum Analog Resolutions	1920 x 1200		
	Maximum Number of Users	1		
	MTBF	145000 hours		
	On-Screen Display	No		
	Port Selection Support	Push Button and Hotkeys		
	Supported Resolutions	up to 1920 x 1200		
Connector(s)	Console Interface(s)	2 - VGA (15 pin, High Density D-Sub) Female Output 1 - 3.5 mm Mini-Jack (3 Position) Female Output 4 - USB Type-A (4 pin) USB 2.0 Female		
	Host Connectors	8 - VGA (15 pin, High Density D-Sub) Female Input 8 - 3.5 mm Mini-Jack (3 Position) Female Input 4 - USB B (4 pin) Female		
	Indicators	LED Indicators	1 - Green - Power 4 - Green - PC Detected 4 - PC Selection Indicators 4 - Red - PC Indicator	
		Power	Center Tip Polarity	Positive
			Input Current	0.8A
			Input Voltage	100 - 240 AC
Output Current	1.5A			

	Output Voltage	12 DC
	Plug Type	M
	Power Consumption (In Watts)	18
	Power Source	AC Adapter Included
Environmental	Humidity	90% RH
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Physical Characteristics	Color	Black
	Enclosure Type	Steel
	Product Depth	5.1 in [130 mm]
	Product Height	2.4 in [6 cm]
	Product Length	8.7 in [22 cm]
	Product Width	5.3 in [13.5 cm]
	Weight of Product	2.7 lb [1.2 kg]
Packaging Information	Package Height	1.1 in [28 mm]
	Package Length	13 in [33 cm]
	Package Width	10 in [25.5 cm]
	Shipping (Package) Weight	3.9 lb [1.8 kg]
What's in the Box	Included in Package	1 - dual VGA USB KVM switch 1 - universal power adapter (NA / EU / UK / AU) 1 - instruction manual

Product appearance and specifications are subject to change without notice.