

4 Port DVI USB KVM Switch with Audio and USB 2.0 Hub

Product ID: SV431DVIUA



This 4 port DVI USB KVM Switch lets you control four USB enabled, DVI capable computers from a single USB keyboard and mouse peripheral set.

Ideal for multimedia applications, the switch supports audio and microphone switching, allowing you to switch between audio/mic channels either independently or simultaneously when switching between computers for KVM control.

The DVI USB KVM switch features an integrated USB 2.0 hub which allows you to use shared USB peripherals from the control point as if the devices were connected directly to the slave computers - an economical solution that lets you use USB peripherals between computers (when selected) without the expense of buying individual peripherals for each slave computer.

Rackmount your KVM switch

If you'd like to mount this KVM switch to your server rack, StarTech.com offers a [1U Rackmount Bracket](#) (sold separately) that turns this KVM into a rackmountable KVM.

This product is TAA compliant and is backed by a Startech.com 3 year warranty with lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Ideal for using desktops, workstations and servers with Flat Panel LCD monitor
- Sharing computers and USB devices in the home/SOHO/multimedia environment
- Switches instantly between PCs

Features

- 4-port DVI USB KVM switch with audio and microphone switching and 2 x USB 2.0 hub ports
- Channel selection/Hub port control by front-panel push buttons
- DVI interface technology supports digital video signal transmission
- Independent/simultaneous audio & mic channel and PC port selection
- USB keyboard and mouse support
- HDCP Compliant

Hardware	Warranty	3 Years
	Audio	Yes
	Cables Included	No
	Daisy-Chain	No
	KVM Ports	4
	Number of Monitors Supported	1
	PC Interface	USB
	PC Video Type	DVI
	Rack-Mountable	Optional
Performance	DVI Support	Yes
	Hot-Key Selection	No
	IP Control	No
	Maximum Analog Resolutions	2560x1600 @ 60Hz
	Maximum Digital Resolutions	1920x1200 @ 60/70Hz
	Maximum Number of Users	1
	On-Screen Display	No
	Port Selection Support	Push Button
Connector(s)	Console Interface(s)	1 - DVI-I (29 pin) Female 2 - 3.5 mm Mini-Jack (3 Position) Female 2 - USB Type-A (4 pin) USB 2.0 Female
	Host Connectors	4 - DVI-I (29 pin) Female 4 - USB B (4 pin) Female 8 - 3.5 mm Mini-Jack (3 Position) Female
	Other Interface(s)	2 - USB Type-A (4 pin) USB 2.0 Female
Software	OS Compatibility	OS independent; No software or drivers required
Power	Center Tip Polarity	Positive
	Input Current	0.4A
	Input Voltage	110V-240V AC
	Output Current	2A
	Output Voltage	5 DC
	Plug Type	N
	Power Consumption (In Watts)	10

	Power Source	AC Adapter Included
Environmental	Humidity	0%~80%
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Physical Characteristics	Color	Black
	Enclosure Type	Steel
	Product Height	4.5 in [115 mm]
	Product Length	10 in [253 mm]
	Product Weight	2.3 lb [1 kg]
	Product Width	1.8 in [45 mm]
Packaging Information	Shipping (Package) Weight	3.4 lb [1.5 kg]
What's in the Box	Included in Package	1 - 4 Port DVI KVM Switch
		4 - Rubber Feet
		1 - Power Adapter
		1 - User Manual

Product appearance and specifications are subject to change without notice.