

# USB VGA KVM Console Extender over CAT5 UTP (500 ft)

Product ID: SV565UTPU



The SV565UTPU USB VGA KVM Console Extender over CAT5 UTP (500 ft) lets you control a server, computer or multiple computers (connected through KVM Switch) over a standard Cat5 or Cat6 UTP network cable connection, at distances of up to 500 ft (150 m) away. PC connection cables are included with this product for a ready out of the box solution.

You can use your existing keyboard, mouse, and monitor to access both the server room and your office computer, saving space and avoiding the need for a dedicated remote console by allowing you to switch between workstation view and KVM view at the remote location.

This product is TAA compliant and backed by a Startech.com 2-year warranty with free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Monitor computer-controlled equipment in a factory or warehouse
- Use one or more servers in a server room from a remote location
- Control remote machines and security monitoring systems

### Features

- PS/2 and USB host PC's supported via the appropriate PS2 or USB KVM cable (USB style included)
- Can be used with a single computer or connected to an existing KVM switch
- Easy installation using industry-standard UTP network cable
- Supports most combo keyboard and mouse sets (including Wireless)
- Intuitive hotkey commands
- Supports auto-switching between host and remote users or dedicated control

<b>Hardware</b>	Warranty	2 Years
	Audio	No
	KVM Ports	2
	Number of Monitors Supported	1
	PC Interface	USB
	PC Video Type	VGA
	Rack-Mountable	No
<b>Performance</b>	IP Control	No
	Max Transfer Distance	150 m (492 ft)
	Supported Resolutions	1280 x 1024 @ 300ft/ 100m 1024 x 768 @ maximum cable length
<b>Connector(s)</b>	Console Interface(s)	1 - VGA (15 pin, High Density D-Sub) Female 2 - USB Type-A (4 pin) USB 2.0 Female
	Host Connectors	1 - VGA (15 pin, High Density D-Sub) Female
	Other Interface(s)	1 - RJ-45 Female
<b>Software</b>	OS Compatibility	OS independent; No software or drivers required
<b>Special Notes / Requirements</b>	<b>Note</b>	Product weights/measurements and connector types indicate a single unit only (either Host or Remote)
<b>Power</b>	Center Tip Polarity	Positive
	Input Current	0.2A
	Input Voltage	110V-240V AC
	Output Current	0.6A
	Output Voltage	9 DC
	Plug Type	M
	Power Consumption (In Watts)	5.4
	Power Source	AC Adapter Included
<b>Environmental</b>	Humidity	0~80% RH
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
<b>Physical Characteristics</b>	Color	Black
	Product Height	0.8 in [20 mm]
	Product Length	3 in [75 mm]

	Product Weight	21.6 oz [612 g]
	Product Width	6.1 in [155 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	3 lb [1.3 kg]
<b>What's in the Box</b>	Included in Package	1 - host unit 1 - remote unit 2 - 6 ft 2-in-1 USB VGA KVM cables 8 - rubber feet 1 - power adapter 1 - instruction manual

Product appearance and specifications are subject to change without notice.