

DC Power Adapter - 12V, 2A

Product ID: SVA12M2NEUA



This 12V DC power supply can provide a power source for any electronic device that has an M-type barrel and requires 12 volts and up to 2 amps of power.

Replace your failed or lost power adapter

The power supply is a perfect replacement for the lost or damaged 12-volt 2-amp power adapter you've used to power your existing electronics.

Keep a spare power adapter on hand

When downtime isn't an option, keeping spare power adapters on hand ensures that you won't be left waiting for a replacement to arrive or have to replace your devices just for the sake of a compatible power source.

This 12V 2A DC power supply is a direct replacement for the power adapters included with the following StarTech.com products:

[80 m VGA to Cat 5 Monitor Extender Kit](#)
[1 km VDSL2 Extender Kit](#)
[40 km Gigabit Single Mode Fiber Media Converter LC](#)
[550 m Gigabit Single Mode Fiber Media Converter LC](#)
[550 m Gigabit Multi Mode Fiber Media Converter SC](#)
[2 km Fiber Media Converter Multi Mode SC](#)
[2 km Multi ModeFiber Media Converter ST](#)
[USB 3.0 Hard DriveEnclosure for 3.5in SATA Drives](#)
[USB 3.0 SATA Hard Drive Docking Station for 2.5 in. or 3.5 in. Drives](#)
[USB 3.1 Single-Bay Dock for 2.5 in. or 3.5 in. HDD](#)
[eSATA or USB 3.0 SATA Hard Drive Dock](#)
[External Docking Station for 2.5 in. or 3.5 in. Hard Drives](#)
[HDMI Over CAT5 HDBaseT Extender](#)
[HDMI Over CAT5 Extender](#)
[VGA Over CAT5 Extender](#)
[2-Port Dual DVI USB KVM Switch](#)
[2-Port DVI VGA Dual Monitor KVM Switch](#)
[2-Port Dual DisplayPort USB KVM Switch](#)
[2-Port Dual VGA KVM Switch](#)
[2-Port Quad DVI KVM Switch](#)
[4-Port Dual DVI KVM Switch](#)
[4-Port DVI VGA Dual Monitor KVM Switch](#)
[4-Port DisplayPort KVM Switch](#)
[4-Port Dual VGA KVM Switch](#)

The SVA12M2NEUA is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Replace a lost or broken 12V DC power supply
- Keep an extra power adapter on hand for your mission-critical devices

Features

- Supports a range of devices that require 12 volts and 2 amps (or less) of power and a M-type barrel connector
- Reduces downtime in the event of a failure, by keeping a spare power adapter on-hand

	Warranty	2 Years
Connector(s)	Output Connectors	1 - M-Type Barrel (Inner Diameter: 2.1 mm, Outer Diameter: 5.5 mm) Plug Output
Power	Center Tip Polarity	Positive
	Input Current	0.6 A
	Input Voltage	100 - 240 AC
	Input Voltage Frequency	50/60Hz
	Output Current	2 A
	Output Voltage	12 DC
	Plug Type	M
	Power Consumption (In Watts)	24
	Power Source	AC Adapter Included
Physical Characteristics	Cable Length	48 in [1219 mm]
	Product Height	1.7 in [4.3 cm]
	Product Length	3 in [75 mm]
	Product Width	1.6 in [40 mm]
	Weight of Product	4.8 oz [137 g]
Packaging Information	Package Height	2.4 in [60 mm]
	Package Length	4.1 in [10.4 cm]
	Package Width	3.5 in [89 mm]
	Shipping (Package) Weight	0.5 lb [0.2 kg]
What's in the Box	Included in Package	1 - universal power adapter (NA, EU, UK, AU)

Product appearance and specifications are subject to change without notice.