

USB 2.0 S-Video and Composite Video Capture Cable

Product ID: SVID2USB2NS



The SVID2USB2NS USB 2.0 S-Video and Composite video Capture Cable lets you connect devices that output S-Video or Composite video to a computer, through an available USB 2.0 port.

The perfect solution for bridging a computer and an S-Video or Composite video source, the capture cable offers real time MPEG 1, MPEG 2 and MPEG 4 recording. Small enough to fit in the palm of your hand, the Capture Cable is a great solution for mobile applications and integrates seamlessly with laptop and desktop computers.

If you require audio with your video capture please see StarTech.com's [S-Video to USB 2.0 Video Capture Cable](#)(SVID2USB2).

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Convert VHS home movies to digital format
- Import recorded videos into your computer system for editing and make your own compilation
- Connect your VCR, camcorder, or any other analog video source to your desktop or notebook PC and capture your video in MPEG 1/2/4 format

Features

- Small and lightweight for portability or on the go applications
- USB 2.0 transfer rates for high quality video capturing
- Choose from MPEG 1 / MPEG 2 / MPEG 4 video encoding
- Up to 30 fps motion capture capability at maximum resolution of 720x480(NTSC) / 720x576(PAL)
- SnapShot function allows you to capture still images
- USB powered device - requires no external power adapter
- Supports NTSC, and PAL
- Control brightness, contrast, and sharpness

Hardware	Warranty	2 Years
	Audio	No
	AV Input	Composite S-Video
	AV Output	USB
	Industry Standards	Video Input - NTSC, PAL, SECAM File Encoding - MPEG 1, MPEG 2, MPEG 4
Performance	Maximum Analog Resolutions	720x480(NTSC) / 720x576(PAL)
	Maximum Data Transfer Rate	480Mbps
	MTBF	100,000 Hours
Connector(s)	Connector A	1 - USB Type-A (4 pin) USB 2.0 Male Output
	Connector B	1 - Composite Video (1 x RCA) Female Input 1 - S-Video (4 pin, Mini-DIN) Female Input
Software	OS Compatibility	Windows® 8/8.1 (32/64bit), 7 (32/64bit), Vista(32/64), XP(32/64), 2000 Windows® Server 2008 R2
Environmental	Humidity	5~95% RH
	Operating Temperature	0°C to 70°C (32°F to 158°F)
	Storage Temperature	-40°C to 85°C (-40°F to 185°F)
Physical Characteristics	Cable Length	34 in [864 mm]
	Color	Black
	Product Height	0.5 in [12 mm]
	Product Length	42 in [1067 mm]
	Product Weight	2.7 oz [76 g]
	Product Width	1.2 in [30 mm]
Packaging Information	Shipping (Package) Weight	1.1 lb [0.5 kg]
What's in the Box	Included in Package	1 - USB Video Capture Cable 1 - Driver CD 1 - Instruction Manual

Product appearance and specifications are subject to change without notice.