

## 6 ft 3-in-1 PS/2 KVM Cable

Product ID: SVPS23N1\_6



The SVPS23N1\_6 6ft 3-in-1 PS/2 KVM switch Cable is constructed of high quality materials and is expertly designed to ensure crystal clear display quality, and reliable connections.

Our universal PS/2 KVM switch cables are designed to prevent tangles and keep your workspace neat, while delivering excellent performance with your StarTech.com or other KVM switch.

### **Works with:**

Compatible StarTech.com KVMs can be found under the Accessories section.

Aten models (CS78, CS9134, CS9138, CS138A, CS88A, CS82A, CS84A, CS12, CS14, CS124A, CS114A)

TrippLite models (B007-008)

Cables to go models (32569, 22391)

IOGear models (GCS82B, GCS138, GCS78KIT, GCS78, GCS138KITUP, GCS138KIT)

Backed by a StarTech.com lifetime warranty.

### Certifications, Reports and Compatibility



### Applications

- KVM switch cable to be used with OmniView, StarView, SwitchView and Apex KVM switches. (Note: Some non-StarView models may require gender changing cable adapters.)

### Features

- KVM (Keyboard-Video-Mouse) switch cables allows you to connect your computers to a KVM switch
- High quality video cable uses coaxial and twisted pair wiring to maintain optimal video signals
- Ferrite core on video cable minimizes electromagnetic interference and provides crystal clear video
- Available in AT- and PS/2-styles in various cable lengths

<b>Kontakt(er)</b>	Warranty	Lifetime
	Connector A	1 - VGA (15-stifts, High Density D-Sub) Hane 2 - PS/2 (6-stifts, Mini-DIN) Hane
	Connector B	1 - VGA (15-stifts, High Density D-Sub) Hona 2 - PS/2 (6-stifts, Mini-DIN) Hane
<b>Utseende</b>	Färg	Svart
	Kabellängd	6 ft [1.8 m]
	Produktlängd	6 ft [1.8 m]
	Produktvikt	13.1 oz [369.7 g]
<b>Förpackning</b>	Fraktvikt (förpackning)	13.3 oz [376.7 g]
<b>Vad det är i lådan</b>	Ingår i paketet	1 - 6 Ft. PS/2 Style 3-in-1 KVM Switch Cable 1 - DB15 male/male gender changer (GC15HSM) 1 - metal part of thumbscrew must be 1.17in(3cm) 1 - THUMBSCREWS MUST BE 1.93 inches long (4.9cm) THUMBSCREWS MUST BE 1.93in(4.9cm)

Product appearance and specifications are subject to change without notice.