

## KM Switch Cable with File Transfer - USB 3.0

Product ID: SVUSB3DSA



The SVUSB3DSA 2-Port USB 3.0 Dual System Swap KVM Switch lets you share video, keyboard/mouse input and transfer files between two Windows® systems, all through a standard USB 3.0 connection to each. Once connected, you can move your mouse cursor naturally between systems for seamless KVM control.

This USB KVM switch features display sharing (extended or mirrored mode) from either computer, turning your second laptop, tablet or desktop into a shared display. Integrated touchscreen support means that if one or both of your connected systems has a touchscreen, you can use touch to control the computer being mirrored or extended.

Integrated support for file transfers makes it easy to share files through the USB 3.0 KVM connection. With the click of a button, a file transfer window opens that allows you to either drag-and-drop or copy / paste files to any directory on the opposite computer. The device also supports clipboard sharing, so you can copy and paste text from one system to another.

The USB 3.0 interface provides a 5 Gbps data channel to ensure fast file transfers and smooth video streaming / sharing operations, while offering backward compatibility with USB 2.0.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Share video card and hard disk resources between two computers with display sharing and file transfer support
- Control two systems with a single keyboard and mouse
- Use a Windows® touch screen tablet or laptop to control a standard non-touch system

### Features

- Keyboard, mouse and display sharing between 2 Windows® systems
- Single USB 3.0 connection per system
- Supports file transfer and clipboard sharing
- Touchscreen control supported

<b>Hardware</b>	Warranty	2 Years
	Cables Included	Yes
	Chipset ID	MCT - WH90
	KVM Ports	2
	PC Interface	USB 3.0
	Rack-Mountable	No
<b>Performance</b>	Hot-Key Selection	No
	IP Control	No
	Maximum Number of Users	1
	On-Screen Display	No
<b>Connector(s)</b>	Host Connectors	2 - USB Type-A (9 pin) USB 3.0 Male
<b>Software</b>	OS Compatibility	Windows® 8 / 8.1 (32/64), 7 (32/64), Vista(32/64), XP(32/64)
<b>Special Notes / Requirements</b>	System and Cable Requirements	Available USB 2.0/3.0 port (USB 3.0 recommended)
		CPU: Intel Core i3 2.8GHz or higher RAM: 2GB memory or higher
<b>Environmental</b>	Humidity	0~85% RH (Non-condensing)
	Operating Temperature	0°C to 50°C (32°F to 122°F)
	Storage Temperature	-10°C to 75°C (14°F to 167°F)
<b>Physical Characteristics</b>	Cable Length	4.9 ft [1.5 m]
	Color	Black
	Enclosure Type	Plastic
	Product Height	0.4 in [9 mm]
	Product Length	1.9 in [49 mm]
	Product Weight	1.3 oz [37 g]
	Product Width	0.7 in [19 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	5.7 oz [161 g]
<b>What's in the Box</b>	Included in Package	1 - USB 3.0 KM switch cable
		1 - Driver CD
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.