

# Dual 4K 60Hz Monitor Thunderbolt 3 Dock with 6x USB 3.0 Ports

Product ID: TB3DOCK2DPPD



Easily transform your Thunderbolt 3 equipped MacBook Pro or Windows laptop into a dual-4K workstation with up to 40Gbps of throughput. The high-quality TB3 dock features six USB 3.0 ports, 85W Power Delivery to charge your laptop, and an SD card reader.

## Create a Dual-4K 60Hz Workstation

This dual-monitor docking station supports 40Gbps speeds and 4K (4096 x 2160) resolution at 60Hz on two monitors, enabling resource-demanding applications on independent displays without draining system resources. The TB3 dock can support 5K (5120 x 2880) resolutions @ 60Hz on a single display.

Connect your laptop to:

- 1 x 4K monitor via the DP Port
- 1 x 4K monitor via the TB3 USB-C Port (1.8 m cable included)

OR

- 1 x 5K monitor via the DP and TB3 USB-C ports

## Easy Installation & Deployment

Simply connect the TB3 dock to your laptop with the included TB3 cable and start working immediately. No time-consuming driver installations are required. Set up a second monitor using the included USB-C to DisplayPort cable adapter, eliminating the need for extra adapters.

## Plenty of Ports Including SD Card Reader

The TB3 docking station offers six USB 3.0 ports, including a Fast-Charge port and USB-C port, an GbE port and audio/microphone port. The built-in SD card reader adds storage not usually available on most docking stations.

## 85W Power Delivery

Using a single cable, the universal laptop docking station provides up to 85W of Power Delivery to power and charge your laptop, and power your peripherals with its 180W power adapter.

TB3DOCK2DPPD is backed by a StarTech.com 3-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Work productively with high-resolution images and video
- Transfer a 4K movie in under 30 seconds
- Transfer 3 hours of 4K GoPro® video in less than a minute
- Edit 4K video on one display, with a full-size preview on the second 4K display

### Features

- Connect dual UHD 4K 60Hz monitors (DP and TB3 USB-C) to your MacBook Pro or Windows laptop with this Thunderbolt 3 dock
- Easy to set up and ready to go with no driver installation or extra adapters required
- Connect more devices with 6x USB 3.0 ports - 1x USB-C and 5x USB-A (incl. 1x Fast-Charge)
- Power and charge your laptop with Power Delivery 2.0 (up to 85W)
- Supports SD 4.0 plus UHS-II with integrated SD card reader, and GbE connectivity with RJ45 port

<b>Hardware</b>	Warranty	3 Years
	4K Support	Yes
	Bus Type	Thunderbolt 3
	Chipset ID	Intel - Alpine Ridge JHL6540 Texas Instruments - TPS65983 Fresco - FL1100EX Intel - WGI210AT C-Media - CM6533 Genesys Logic - GL3226
	Displays Supported	2
	Fast-Charge Port(s)	Yes
	Industry Standards	Thunderbolt 3 USB Battery Charging Specification Rev. 1.2 IEEE 802.3, IEEE 802.3u, IEEE 802.3ab USB 3.0 - Backward compatible with USB 2.0 and 1.1
	<b>Performance</b>	
Auto MDIX	Yes	
Compatible Networks	10/100/1000 Mbps	
Full Duplex Support	Yes	
Maximum Data Transfer Rate	40 Gbps (Thunderbolt 3) 10 Gbps (USB 3.1 Gen 2) 5 Gbps (USB 3.0) 2 Gbps (Ethernet; Full-Duplex)	
Maximum Digital Resolutions	Dual displays - DisplayPort and Thunderbolt 3 USB-C - 4096 x 2160p / 3840 x 2160p at 60Hz Single 4K display - DisplayPort or Thunderbolt 3 USB-C - 4096 x 2160p / 3840 x 2160p at 60Hz Single 5K (5120 x 2880p) display (through Thunderbolt 3 USB-C port)	
Memory Media Type	SD/MMC (Secure Digital/Multimedia Card) SDHC (Secure Digital High Capacity) SDXC (Secure Digital eXtended Capacity) microSD (Micro Secure Digital) (adapter required) microSDHC (Micro Secure Digital High Capacity) (adapter required) microSDXC (Micro Secure Digital eXtended Capacity) (adapter required)	
PXE	Yes	
Type and Rate	Thunderbolt 3 - 40 Gbit/s	
UASP Support	Yes	

<b>Connector(s)</b>	Connector Type(s)	<p>2 - Thunderbolt™ 3 USB-C (24-pin) (40Gbps) Female</p> <p>1 - DisplayPort (20 pin) Female</p> <p>1 - USB Type-C (24 pin) USB 3.0 (5Gbps) Female</p> <p>1 - USB 3.0 A (Fast-Charge, 9 pin) Female</p> <p>4 - USB Type-A (9 pin) USB 3.0 Female</p> <p>1 - RJ-45 Female</p> <p>1 - 3.5 mm Mini-Jack (3 Position) Female</p>
<b>Software</b>	OS Compatibility	<p>Windows® 8, 8.1, 10</p> <p>macOS 10.12 - 10.15</p>
<b>Special Notes / Requirements</b>	<b>Note</b>	<p>A 4K-capable display is required to achieve 4K x 2K resolution (4K is also known as 4K x 2K).</p> <p>When connecting a display to one of the Thunderbolt 3 USB-C ports, a USB-C video adapter might be required depending on the input of your display.</p> <p>USB 3.0 is also known as USB 3.1 Gen 1; this connectivity standard offers speeds up to 5Gbps. USB 3.1 Gen 2 offers speeds up to 10Gbps.</p> <p>System and Cable Requirements</p> <p>Thunderbolt 3 equipped computer with a Thunderbolt 3 port.</p> <p>Your laptop's Thunderbolt 3 port must support USB Power Delivery 2.0 in order to power and charge your laptop.</p>
<b>Power</b>	Center Tip Polarity	Positive
	Input Current	2.5 A
	Input Voltage	100 - 240 AC
	Output Current	9 A
	Output Voltage	20V DC
	Plug Type	N
	Power Consumption (In Watts)	180
	Power Delivery	85W
	Power Source	AC Adapter Included
<b>Environmental</b>	Humidity	0~95% RH
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-20°C to 70°C (-4°F to 158°F)
<b>Physical Characteristics</b>	Color	Space Gray
	Enclosure Type	Aluminum

	Product Height	1.3 in [3.4 cm]
	Product Length	8.7 in [22.2 cm]
	Product Width	3.4 in [87 mm]
	Weight of Product	17.4 oz [492 g]
<b>Packaging Information</b>	Package Height	3.5 in [90 mm]
	Package Length	11.6 in [29.5 cm]
	Package Width	5.7 in [14.5 cm]
	Shipping (Package) Weight	3.4 lb [1.5 kg]
<b>What's in the Box</b>	Included in Package	1 - docking station
		1 - Thunderbolt 3 cable
		1 - USB-C to DisplayPort cable
		1 - universal power adapter
		2 - power cords (NA/JP, ANZ)
		1 - instruction manual

Product appearance and specifications are subject to change without notice.