

## 1m White Thunderbolt Cable - M/M

Product ID: TBOLTMM1MW



This 1m (3.28ft) White Thunderbolt™ cable offers a dependable, high-quality solution for harnessing the speed and power of Thunderbolt technology while combining both data and video into a single high-performance cable.

The TBOLTMM1MW supports both Thunderbolt 1 (10Gbps) and Thunderbolt 2 (20Gbps) devices and can link compatible devices as part of a daisy-chained connection. Plus, with bi-directional data transfer capability and support for power delivery (for bus-powered devices), this Thunderbolt cable offers the performance needed for optimal connections.

Expertly designed and constructed of only top quality material, this high performance cable is backed by StarTech.com's 2-year Warranty.

### Certifications, Reports and Compatibility



### Applications

- Connect a Thunderbolt-equipped external drive enclosure or RAID array
- Connect two Thunderbolt-equipped Mac® computers, for Target Disk Mode file transfers
- Connect a Thunderbolt-equipped MacBook Pro® to an iMac®, to use the iMac as the display for the MacBook Pro

### Features

- Compatible with Thunderbolt 1 and Thunderbolt 2 specifications
- Supports Power-over-cable, for bus-powered Thunderbolt devices
- Supports native peer-to-peer file sharing when supported by the OS

<b>Hardware</b>	Warranty	2 Years
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
<b>Performance</b>	Type and Rate	Thunderbolt 2 - 20 Gbit/s
<b>Connector(s)</b>	Connector A	1 - Thunderbolt™ (20-pin) Male
	Connector B	1 - Thunderbolt™ (20-pin) Male
<b>Power</b>	Power Delivery	10W
<b>Physical Characteristics</b>	Cable Length	3.3 ft [1 m]
	Color	White
	Product Height	0.3 in [8 mm]
	Product Length	3.3 ft [1 m]
	Product Weight	1.4 oz [40 g]
	Product Width	0.4 in [11 mm]
	Wire Gauge	34 AWG
<b>Packaging Information</b>	Package Quantity	1
	Shipping (Package) Weight	1.6 oz [45 g]
<b>What's in the Box</b>	Included in Package	1 - 1m White Thunderbolt Cable - M/M

Product appearance and specifications are subject to change without notice.