

2U Adjustable Mounting Depth Vented Sliding Rack Mount Shelf – 50lbs / 22.7kg

Product ID: UNISLDSHF19



The UNISLDSHF19 19in Vented Adjustable Mounting Depth Sliding Server Rack Cabinet Shelf offers a simple way to install non rack mountable equipment into a server cabinet or open server rack. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Offering a weight capacity of up to 50 lbs (22.7 kg), the sliding rack shelf features a ventilated, cold-rolled steel shelf on two locking adjustable rails which allow the shelf to be installed into cabinets or racks with mounting depths from 20in (510mm) to 30in (744mm). The locking feature locks the shelf 3/4 of the way out, preventing the shelf from accidentally falling out of the rack or sliding back in before maintenance is complete.

Backed by a StarTech.com lifetime warranty.

Certifications, Reports and Compatibility



Applications

- For use with all 19" wide Server Racks and Cabinets
- Add a sliding rack mounting option for non rack mountable equipment

Features

- Constructed from 16 gauge cold rolled steel
- Highly ventilated to reduce airflow impedance
- TAA compliant for GSA Schedule purchases
- Supports up to 22.7 kg (50 lbs) of equipment
- Meets EIA RS-310-C standards
- Locking rails prevent the shelf from sliding all the way out
- Includes Mounting screws and nuts

Hardware	Warranty	Lifetime
	Airflow Rate	Vented
	Cable Management	No
	Frame Type	Steel
	Industry Standards	EIA RS310-C
	U Height	2U
Performance	Weight Capacity (Stationary)	50.1 lb [22.7 kg]
Physical Characteristics	Color	Black
	Maximum Mounting Depth	29.3 in [744 mm]
	Minimum Mounting Depth	20.1 in [510 mm]
	Weight of Product	14.1 lb [6.4 kg]
Packaging Information	Package Height	5.4 in [13.8 cm]
	Package Length	26.8 in [68 cm]
	Package Width	20.7 in [52.7 cm]
	Shipping (Package) Weight	18.5 lb [8.4 kg]
What's in the Box	Included in Package	1 - Sliding Shelf 8 - M6 Screws 8 - M6 Cage Nuts

Product appearance and specifications are subject to change without notice.