

2U Vented Sliding Rack Shelf w/ Cable Management Arm & Adjustable Mounting Depth - 125lbs / 56.7kg

Product ID: UNISLDSHF19M



The UNISLDSHF19M Adjustable Sliding Rack Shelf lets you add a vented, sliding shelf with cable management into virtually any 4-post server rack or cabinet. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The adjustable mounting depth design allows the shelf to be installed easily into server cabinets with mounting depths from 27.7in (702.2mm) to 31.6in (802.2mm). The sliding rails also offer a locking mechanism to stop the shelf from sliding out too far, or sliding back into the rack before maintenance is complete.

Offering a weight capacity of up to 125 lbs (56.7 kg), this sliding rack shelf features a ventilated, cold-rolled steel construction for increased airflow and durability in your server room or wiring closet installations.

For ease in routing cables neatly through your rack, we've included a reversible cable management arm that can be attached to the back of the shelf, plus an adjustable bezel to keep your equipment where you want it on the shelf.

Backed by a StarTech.com 2-year warranty.

Certifications, Reports and Compatibility



Applications

- Supply additional storage space for hardware or non-rackmount equipment and peripherals
- Install into virtually any standard 4-post rack or cabinet

Features

- Supports up to 125lbs (56.7kg)
- Adjustable mounting depth from 27.7in (702.2mm) to 31.6in (802.2mm)
- TAA compliant for GSA Schedule purchases
- Includes a reversible cable management arm
- Vented shelf for increased airflow
- Sliding rails with locks to prevent the shelf from sliding out too far
- Sturdy, 2mm cold-rolled steel construction

Hardware	Warranty	2 Years
	Airflow Rate	Vented
	Cable Management	Yes
	Industry Standards	EIA RS310-D
	Mounting Options	Front Mount (Front and Rear)
	U Height	2U
Performance	Weight Capacity (Stationary)	125.3 lb [56.7 kg]
Physical Characteristics	Color	Black
	Enclosure Type	Steel
	Maximum Mounting Depth	31.6 in [802.2 mm]
	Minimum Mounting Depth	27.6 in [702.2 mm]
	Rail Thickness	0.1 in [2 mm]
	Weight of Product	18 lb [8.2 kg]
Packaging Information	Package Height	4.4 in [11.3 cm]
	Package Length	29.1 in [74 cm]
	Package Width	21.7 in [55.1 cm]
	Shipping (Package) Weight	22.2 lb [10.1 kg]
What's in the Box	Included in Package	1 - Shelf Assembly
		2 - Ear Hook and Slide Assembly (Left / Right)
		2 - Ear Hook Bracket (Left / Right)
		1 - Cable Management Assembly
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.