

35m USB 2.0 Active Extension Cable - M/F

Product ID: USB2AAEXT35M



The USB2AAEXT35M 35-meter Active USB 2.0 Extension Cable, offers one USB type-A (male) connector and one USB type-A (female) connector, and provides an active extension of USB 2.0 devices of up to 35-meters (115-feet).

An all-in-one cable for overcoming distance restrictions as well as power source limitations, the active USB 2.0 extension cable incorporates bus-powered active circuitry to ensure performance beyond the length limits of standard USB cables. If necessary, the USB device can be powered from a wall outlet using the Universal AC power adapter provided with the cable.

The USB2AAEXT35M extension cable (USB Extender) supports transfer rates of up to 480 Mbps, and is backed by StarTech.com's 2-year Warranty.

Certifications, Reports and Compatibility



Applications

- Extend the distance of USB peripherals beyond the USB 2.0 5-meter limitation
- Backward compatible with USB 1.1

Features

- Fully shielded for error-free connections
- Plug-and-play, no driver required
- USB bus-powered
- Universal external power source also included
- Blue LED indicator x1 for Extension Cable and USB port connection status monitoring
- Compatible with PC Windows® 8/7/Vista/XP and Mac computer systems

Hårdvara	Warranty	2 Years
	Kabelmanteltyp	PVC - Polyvinyl Chloride
	Kontaktplätering	Nickel
Kontakt(er)	Connector A	1 - USB Type-A (4-stifts) USB 2.0 Hane
	Connector B	1 - USB Type-A (4-stifts) USB 2.0 Hona
Ström	Inspänning	110V-240V AC
	Inström	0.35 A
	Kontakttyp	H
	Polaritet på mittpol	Positiv
	Power Source	AC-adapter medföljer
	Strömförbrukning	5
	Utspänning	5 DC
	Utström	1A
Utseende	Färg	Svart
	Kabellängd	114.8 ft [35 m]
	Produktlängd	114.8 ft [35 m]
	Produktvikt	3.1 lb [1.4 kg]
Förpackning	Förpackningsantal	1
	Fraktvikt (förpackning)	3.8 lb [1.7 kg]
Vad det är i lådan	Ingår i paketet	1 - 35 m USB 2.0 Active Extension Cable - M/F 1 - Universal Power Adapter 1 - Plug Adapters for North America, UK, Europe, and Australia

Product appearance and specifications are subject to change without notice.