

## 10m/30ft Active USB 2.0 A to B Cable - M/M

Product ID: USB2HAB30AC



The USB2HAB30AC 30-foot USB A to B cable features one USB type-A (male) connector and one USB type-B (male) connector, providing a high quality connection to USB 2.0 peripherals.

This 30-foot USB cable incorporates an equalizing chip, which enables it to perform beyond the limits of standard USB cables and communicate with peripherals up to 30ft away.

Expertly designed with top quality materials for high durability, backed by a 2 Year Warranty.

### Certifications, Reports and Compatibility



### Applications

- Connecting USB 2.0/1.1 devices up to 30ft away to a computer

### Features

- Built-in equalizing chip enables USB 2.0 connections spanning 30ft

<b>Hardware</b>	Warranty	2 Years
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
<b>Performance</b>	Maximum Cable Length	32.8 ft [10 m]
	Type and Rate	USB 2.0 - 480 Mbit/s
<b>Connector(s)</b>	Connector A	1 - USB Type-A (4 pin) USB 2.0 Male
	Connector B	1 - USB B (4 pin) Male
<b>Special Notes / Requirements</b>	<b>Note</b>	USB2HAB30AC draws a maximum of 70mA for powering internal active circuitry
<b>Physical Characteristics</b>	Cable Length	32.8 ft [10 m]
	Color	Black
	Product Length	32.8 ft [10 m]
	Product Weight	15.5 oz [438 g]
	Wire Gauge	28 AWG
<b>Packaging Information</b>	Package Quantity	1
	Shipping (Package) Weight	17.8 oz [505 g]
<b>What's in the Box</b>	Included in Package	1 - 10m/30ft High Speed Certified USB 2.0 Cable

Product appearance and specifications are subject to change without notice.