

## 3m USB 2.0 A to B Cable - M/M

Product ID: USB2HAB3M



The USB2HAB3M 3-meter USB A-to-B cable features one USB 'A' male connector and one USB 'B' male connector, providing a high quality connection to USB 2.0 peripherals such as USB printers, scanners or external USB hard drives.

Constructed of only top quality materials and expertly designed for durability, this USB 2.0 A-B cable is backed by StarTech.com's Lifetime Warranty.

### Certifications, Reports and Compatibility



### Applications

- Use with any USB 2.0 rated device or add-on card
- Compatible with USB1.1 devices
- Replace worn-out or missing USB cables with this high quality cable

### Features

- High quality USB 'A' and USB 'B' connectors
- Supports USB 2.0 data transfer rates up to 480 Mbps

<b>Hardware</b>	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
<b>Connector(s)</b>	Connector A	1 - USB Type-A (4 pin) USB 2.0 Male
	Connector B	1 - USB B (4 pin) Male
<b>Physical Characteristics</b>	Cable Length	3 m [9.8 ft]
	Color	Black
	Product Length	3 m [9.8 ft]
	Weight of Product	104.2 g [3.7 oz]
	Wire Gauge	24/28 AWG
<b>Packaging Information</b>	Package Height	10 mm [0.4 in]
	Package Length	22.2 cm [8.7 in]
	Package Quantity	1
	Package Width	12.5 cm [4.9 in]
	Shipping (Package) Weight	105.2 g [3.7 oz]
<b>What's in the Box</b>	Included in Package	1 - 3 m USB 2.0 A to B Cable - M/M

Product appearance and specifications are subject to change without notice.