

USB-C to USB-C Cable w/ 5A PD - M/M - 6 ft. (1.8 m) - USB 3.0 (5Gbps) - USB-IF Certified

Product ID: USB315C5C6



With up to 5A (100W) of power output, you can use this USB-C™ to USB-C cable to power and charge a USB-C laptop, such as your Apple MacBook Pro, MacBook or Chromebook Pixel™, using a USB-C wall charger, car charger or power bank. Or, you can power your laptop from a USB-C docking station. You can also power your USB-C hard drive from the USB-C port on your laptop.

Fast-charge your mobile devices

The 5A of Power Delivery lets you charge your mobile devices faster than with a regular USB-C 3.0 cable, which is perfect for people on the move. Decrease your charge times and make sure your mobile devices are ready, whenever you need them while you're on the road.

Deliver full 4K video

The cable supports full 4K 60Hz video and DisplayPort 1.2 and is compatible with existing DisplayPort displays. It's ideal for connecting your docking station or laptop to a monitor with astonishing resolution, contrast, and color depth for amazing detail.

Provide superior connections with USB-IF certified cables

The USB Type-C cable has undergone rigorous compliance testing and is certified by USB-IF (USB Implementers Forum) to meet all USB 3.0 specifications. This includes all environmental, electrical and mechanical standards, which ensures a reliable and high-quality cable for all of your USB-C devices.

The USB315C5C6 from StarTech.com is backed by a 2-year warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Power your USB-C hard drive from a laptop
- Power your USB-C laptop from a charger or power bank
- Charge your USB-C laptop from a docking station
- Fast-charge your USB-C mobile devices from a charger
- Sync your USB-C mobile devices with a laptop
- Output full 4K 60Hz video and DisplayPort 1.2 with DP enabled USB-C devices

Features

- USB-IF Certified
- Provides up to 5 amps of power output for fast charging your mobile devices, or powering your USB-C laptop
- Supports data transfer rates up to 5Gbps
- Thunderbolt™ 3 port compatible
- Guaranteed reliability with our 2-year warranty

Hardware	Warranty	2 Years
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
Performance	Maximum Digital Resolutions	4K @ 60Hz
	Type and Rate	USB 3.0 - 5 Gbit/s
Connector(s)	Connector A	1 - USB Type-C (24 pin) USB 3.0 (5Gbps) Male
	Connector B	1 - USB Type-C (24 pin) USB 3.0 (5Gbps) Male
Power	Power Delivery	100W
Physical Characteristics	Cable Length	6 ft [1.8 m]
	Color	Black
	Connector Style	Straight
	Product Height	0.2 in [0.5 cm]
	Product Length	6 ft [1.8 m]
	Product Width	0.5 in [12 mm]
	Weight of Product	3 oz [85 g]
Packaging Information	Wire Gauge	21 AWG
	Package Height	0.4 in [10 mm]
	Package Length	8.9 in [22.5 cm]
	Package Width	7.9 in [20 cm]
What's in the Box	Shipping (Package) Weight	3.3 oz [93 g]
	Included in Package	1 - USB-C cable

Product appearance and specifications are subject to change without notice.