

## 2m (6 ft) Certified SuperSpeed USB 3.0 A to B Cable - M/M

Product ID: USB3CAB2M



The USB3CAB2M 2-meter USB 3.0 A-to-B cable provides a high quality connection between peripheral devices that feature a USB 3.0 type-B port, such as hard drive enclosures, card readers, docking stations and video capture devices and a USB-capable computer.

This cable is USB-IF certified to USB 3.0 specifications, guaranteeing a dependable, long-lasting connection to your USB 'B' devices and is backed by StarTech.com's Lifetime Warranty.

### Certifications, Reports and Compatibility



### Applications

- Connect a SuperSpeed USB 3.0 Type B peripheral (hard drive enclosure, card reader, docking station, video capture device, etc.) to a USB 3.0 capable desktop, laptop, or server

### Features

- 1x USB 'A' male connector
- 1x USB 'B' male connector
- USB-IF Certified SuperSpeed USB 3.0
- Data transfer rates up to 5Gbps
- Aluminum-Mylar Foil with Braided Shielding
- Molded connectors with strain relief
- Backward compatible with USB 2.0

<b>Hardware</b>	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
<b>Performance</b>	Type and Rate	USB 3.0 - 5 Gbit/s
<b>Connector(s)</b>	Connector A	1 - USB Type-A (9 pin) USB 3.0 Male
	Connector B	1 - USB Type-B (9 pin) USB 3.0 Male
<b>Environmental</b>	Operating Temperature	-20°C to 80°C (-4°F to 176°F)
	Storage Temperature	-20°C to 80°C (-4°F to 176°F)
<b>Physical Characteristics</b>	Cable Length	6.6 ft [2 m]
	Color	Black
	Connector Style	Straight
	Product Length	6.6 ft [2 m]
	Product Weight	3.2 oz [90 g]
	Wire Gauge	24/28 AWG
<b>Packaging Information</b>	Package Quantity	1
	Shipping (Package) Weight	3.5 oz [99 g]
<b>What's in the Box</b>	Included in Package	1 - 2m USB 3.0 Certified A to B Cable - M/M

Product appearance and specifications are subject to change without notice.