


# KVM Docking Station for Two Laptops - Share Keyboard, Mouse, Dual Monitors, and Files - USB 3.0

Product ID: USB3DDOCKFT



This TAA compliant KVM USB 3.0 docking station for two laptops functions like a KVM switch, enabling you to share your keyboard, video, and mouse, and transfer files between your docked laptops.



## Shared Docking with KVM Control

Connect two laptops to this dock to share dual monitors, a keyboard, mouse, and peripherals. This KVM docking station lets you control two laptops and share two monitors and several peripherals between them while they're docked. The docking station features:

- 2 x monitor ports (DP and HDMI)\*
- 5 x USB 3.0 ports
- 1 x Gigabit Ethernet port
- 1 x headset port

## Transfer Files Between Your Laptops

Instead of transferring files to the cloud or external storage, the docking station lets you quickly and securely transfer data between your docked laptops, using Windows Easy Transfer or the included PCLing software.



## Fast-Charge Your Mobile Devices

The USB 3.0 dock's always-on USB fast-charge port lets you charge your tablets and other mobile devices, even if your laptops aren't docked.



## Convenient Display Options

This USB docking station gives you the option to connect a single 4K display instead of dual displays. Set your laptop workstation up with dual monitors (1x DisplayPort, 1x HDMI), or for higher resolutions, connect either a single HDMI or 4K DisplayPort monitor.

### Maximum Supported Resolutions\*

Video Output Configuration	Max DisplayPort Resolution	Max HDMI Resolution
DisplayPort and HDMI (Two Displays)	2048 x 1152p	2048 x 1152p
DisplayPort (Single Display)	3840 x 2160p (4K)	N/A
HDMI (Single Display)	N/A	2560 x 1440p

*\*Lower resolutions are also supported. For example, if the max is 3840 x 2160p (4K), it also supports 2560 x 1600p and 2560 x 1440p.*

## Easy Installation, Simple Switching

Compatible with Mac and Windows® USB 3.0 equipped laptops, the KVM docking station includes two USB 3.0 cables for quick installation and features an easy-access button for easy switching between laptops.

StarTech.com laptop docking stations offer cost savings and faster deployment with just a single cable. This USB 3.0 Docking Station is backed by a competitive 3-year warranty and free lifetime Technical Support.

### Certifications, Reports and Compatibility



### Applications

- Classrooms
- Computer Labs
- Network and Systems Administration

### Features

- Control up to two host laptops using one dual-monitor workstation
- Speed up your workflow with file sharing between host computers
- Charge your devices without a laptop connection using the always-on USB fast-charge port
- Set up easily with the included file sharing software and two USB 3.0 cables

<b>Hardware</b>	Warranty	3 Years
	4K Support	Yes
	Bus Type	USB 3.0
	Chipset ID	DisplayLink - DL-5900 VIA/VLI - VL812
	Displays Supported	2
	Fast-Charge Port(s)	Yes
	Industry Standards	USB Battery Charging Specification Rev. 1.2 IEEE 802.3, IEEE 802.3u, IEEE 802.3ab USB 3.0 - Backward compatible with USB 2.0/1.1
<b>Performance</b>	Auto MDIX	Yes
	Compatible Networks	10/100/1000 Mbps
	Full Duplex Support	Yes
	Maximum Data Transfer Rate	5 Gbps (USB 3.0) 2 Gbps (Ethernet; Full-Duplex)
	Maximum Digital Resolutions	3840 x 2160 @ 30Hz (DisplayPort - Single Display)  2560 x 1440 (HDMI - Single Display)  2048 x 1152 and 2048 x 1152 (DisplayPort and HDMI - Two Displays)  Lower resolutions are also supported. For example, if the max is 3840 x 2160p (4K), it also supports 2560 x 1600p and 2560 x 1440p.
	Type and Rate	USB 3.0 - 5 Gbit/s
	UASP Support	Yes
<b>Connector(s)</b>	Connector Type(s)	1 - DisplayPort (20 pin) Female  1 - HDMI (19 pin) Female  1 - USB 3.0 A (Fast-Charge, 9 pin, SuperSpeed) Female  4 - USB Type-A (9 pin) USB 3.0 Female  1 - RJ-45 Female  1 - 3.5 mm Mini-Jack (4 Position) Female  2 - USB Type-B (9 pin) USB 3.0 Female  1 - Security Lock Slot Female

<b>Software</b>	OS Compatibility	Windows® 7, 8, 8.1, 10 macOS 10.8 - 10.12, 10.14 Chrome OS™ v55+
<b>Special Notes / Requirements</b>	<b>Note</b>	A 4K-capable DisplayPort display is required to achieve 4Kx2K resolutions  If connected to a USB 2.0 host port, or if using a USB 2.0 host connection cable, performance may be limited (USB 3.0 host cables included)  USB 3.0 is also known as USB 3.1 Gen 1; this connectivity standard offers speeds up to 5Gbps  PCLinq can be used in any operating system that the dock supports. Windows Easy Transfer can only be used in Windows 8.1, 8, and 7
	System and Cable Requirements	Two USB-enabled computers with an available USB 3.0 port on each computer (host)
<b>Indicators</b>	LED Indicators	1 - Link (Green)  1 - Activity (Amber)
<b>Power</b>	Center Tip Polarity	Positive
	Input Current	1.5 A
	Input Voltage	100 ~ 240 AC
	Output Current	6.5 A
	Output Voltage	5 DC
	Plug Type	N
	Power Consumption (In Watts)	32.5
	Power Source	AC Adapter Included
<b>Environmental</b>	Humidity	0~90% RH
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-10°C to 80°C (14°F to 176°F)
<b>Physical Characteristics</b>	Color	Black & Silver
	Enclosure Type	Plastic
	Product Height	1.3 in [3.4 cm]
	Product Length	10.6 in [27 cm]
	Product Width	3.2 in [82 mm]
	Weight of Product	13.2 oz [374 g]

<b>Packaging Information</b>	Package Height	2.8 in [70 mm]
	Package Length	11.7 in [29.6 cm]
	Package Width	6.4 in [16.2 cm]
	Shipping (Package) Weight	2.5 lb [1.1 kg]
<b>What's in the Box</b>	Included in Package	1 - laptop docking station
		2 - 3.3 ft [1 m] USB 3.0 host cables
		1 - universal power adapter (NA/JP, EU, UK, ANZ)
		1 - instruction manual

Product appearance and specifications are subject to change without notice.