

## USB 3.0 to eSATA HDD / SSD / ODD Adapter Cable - 3ft eSATA Hard Drive to USB 3.0 Adapter Cable - SATA 6 Gbps

Product ID: USB3S2ESATA3



The USB3S2ESATA3 USB 3.0 to eSATA drive cable lets you connect any external eSATA hard drive, solid state drive, or optical disc drive to your USB-enabled computer system -- a great solution for computers that don't natively support eSATA, such as MacBook® and Ultrabook™ computers.

To maximize performance and utilize the speed potential of your SATA 6 Gbps drives, the USB 3.0 to eSATA adapter is compatible with SATA revisions I/II/III and supports transfer speeds up to 5 Gbps through USB 3.0.

With support for Blu-ray/DVD/CD ATAPI / ODD drives and large capacity HDD / SSDs (tested up to 4TB) the USB to eSATA adapter cable is compatible with virtually any eSATA device, and can greatly increase the storage/backup capabilities of your computer.

The USB 3.0 to eSATA drive cable ensures a hassle-free connection with simple plug-and-play installation, plus the cable is the perfect length (1-meter, end-to-end) for easily accessing the rear panel USB ports on your computer.

The USB3S2ESATA3 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certificazioni, report e compatibilità



### Applicazioni

- Connect an external eSATA drive to a computer system that only has USB
- Carry with your laptop and eSATA drive for an on the go storage solution
- Swap an eSATA drive between computers systems that do not have eSATA

### Caratteristiche

- Compatible with USB 3.0/2.0/1.1 (5 Gbps / 480 Mbps / 1.5 Mbps)
- eSATA interface compliant with SATA revision 3 and other SATA revisions, with supported data transfer rates up to 6 Gbps
- Supports hard drives (HDD), solid state drives (SSD) and optical disc drives (ODD)
- 1x eSATA connector, 1x USB 3.0 connector with integrated 1m (3.3ft) cable
- No driver or software installation required
- Plug-and-Play and Hot-Swap compatible

<b>Hardware</b>	Warranty	2 Years
	Bus Type	USB 3.0
	Chipset ID	ASMedia - ASM1153E
	Compatible Drive Types	SATA
	Number of Drives	1
<b>Performance</b>	4Kn Support	Yes
	Hot Swap Capability	Yes
	Max Drive Capacity	Currently tested with up to 4TB 7200 RPM hard drives
	Maximum Data Transfer Rate	5 Gbps
	Port Multiplier	No
	Type and Rate	USB 3.0 - 5 Gbit/s SATA III (6 Gbps)
	UASP Support	No
<b>Connector(s)</b>	Drive Connectors	1 - eSATA (7 pin, Data) Female
	Host Connectors	1 - USB Type-A (9 pin) USB 3.0 Male
<b>Software</b>	OS Compatibility	OS independent; No software or drivers required
<b>Environmental</b>	Humidity	40%-85%RH
	Operating Temperature	0°C to 60°C (32°F to 140°F)
	Storage Temperature	-10°C to 70°C (14°F to 158°F)
<b>Physical Characteristics</b>	Product Height	0.4 in [10 mm]
	Product Length	35.8 in [910 mm]
	Product Weight	2.4 oz [67.5 g]
	Product Width	0.9 in [24 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	2.8 oz [80 g]
<b>What's in the Box</b>	Included in Package	1 - USB 3.0 to eSATA Adapter Cable 1 - Installation guide

L'aspetto e le specifiche dell'articolo sono soggetti a modifiche senza preavviso.