

3m Black SuperSpeed USB 3.0 Cable A to B - M/M

Product ID: USB3SAB3MBK



The USB3SAB3MBK 3m Black USB 3.0 A-to-B cable allows you to connect your USB 3.0 type-B devices, such as your hard drive enclosures, card readers, docking stations and video capture devices, up to 3 meters away from your computer.

The USB 3.0 cable features high quality Shielded Twisted Pair (STP) construction, which helps to prevent electro-magnetic interference and ensures reliable data communication.

The 3m cable is backed by StarTech.com's Lifetime Warranty, providing guaranteed quality and reliability.

Certifications, Reports and Compatibility



Applications

- Connect a USB 3.0 Type B peripheral (hard drive enclosure, card reader, docking station, video capture device, etc.) up to 3m away from your USB 3.0 capable desktop, laptop, or server

Features

- Designed and constructed to SuperSpeed USB 3.0 Specifications
- Offers 3m in cable length
- Molded connectors with strain relief
- Data transfer rates up to 5Gbps

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Foil shielded twisted pair
Performance	Type and Rate	USB 3.0 - 5 Gbit/s
Connector(s)	Connector A	1 - USB Type-A (9 pin) USB 3.0 Male
	Connector B	1 - USB Type-B (9 pin) USB 3.0 Male
Physical Characteristics	Cable Length	3 m [9.8 ft]
	Color	Black
	Connector Style	Straight
	Product Height	12 mm [0.5 in]
	Product Length	3 m [9.8 ft]
	Product Weight	128 g [4.5 oz]
	Wire Gauge	28 AWG
Packaging Information	Package Quantity	1
	Shipping (Package) Weight	133 g [4.7 oz]
What's in the Box	Included in Package	1 - 3m Black SuperSpeed USB 3.0 Cable A to B - M/M

Product appearance and specifications are subject to change without notice.