

# Dual-Monitor USB 3.0 Docking Station with DVI and Vertical Stand

Product ID: USB3SDOCKDD



This dual-monitor USB 3.0 docking station turns your laptop into a dual-monitor workstation with flexible setup options.

## Display Flexibility

The dual-DVI docking station adds dual-monitor support to your workstation, with resolution support up to 2048x1152. With more screen space, you can simultaneously access multiple applications and reference material on one display while composing on the other. To ensure the USB 3.0 dock supports a variety of displays, two display adapters (DVI to VGA and DVI to HDMI) are included.



## Powerful Connections and Fast Device Charging

Transform your laptop into a workstation that supports all of your peripherals. This docking station features five USB 3.0 (USB 3.1 Gen 1) ports. The two front-facing USB ports are USB fast-charge ports (USB Battery Charging Specification 1.2). These accessible ports charge your mobile devices faster than standard USB ports, with or without your laptop connected to the dock. The dock also has a GbE port, headset jack and separate 3.5 mm audio and mic ports, so you'll have all the connections you need.



## Save Desktop Space

You can free up valuable desk space by positioning the dock vertically on your work surface using the included (optional) stand.

The USB3SDOCKDD is backed by a 3-year StarTech.com warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Use dual displays to work on multiple documents simultaneously in office applications
- View multiple monitors at a glance, in financial or investment firms
- Create a quick-connect workstation that supports your existing HDMI, VGA, and DVI monitors

### Features

- Dock your USB 3.0 equipped Mac or Windows laptop with support for several dual monitor configurations using the included video adapters
- Connect and charge your USB devices with 5x USB 3.0 ports, including two Fast-Charge USB ports
- Save space on your desktop by placing the dock in a vertical orientation with the included dock stand
- Add wired network connectivity and audio devices with the Gigabit Ethernet RJ-45 port and headset jack.

<b>Hardware</b>	Warranty	3 Years
	4K Support	No
	Bus Type	USB 3.0
	Chipset ID	DisplayLink - DL-3900 Genesys Logic - GL3520 VIA/VLI - VL817
	Displays Supported	2
	Fast-Charge Port(s)	Yes
	Industry Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3ab USB Battery Charging Specification Rev. 1.2 USB 3.0 - Hub ports support USB 2.0/1.1 backward-compatibility
<b>Performance</b>	Auto MDIX	Yes
	Compatible Networks	10/100/1000 Mbps
	Full Duplex Support	Yes
	Maximum Analog Resolutions	2048x1152 (VGA)
	Maximum Data Transfer Rate	5 Gbps (USB 3.0) 2 Gbps (Ethernet; Full-Duplex)
	Maximum Digital Resolutions	2048x1152 (Dual-Link DVI/HDMI) Lower resolutions are also supported.
	Type and Rate	USB 3.0 - 5 Gbit/s
	UASP Support	Yes
<b>Connector(s)</b>	Connector Type(s)	1 - DVI-D (25 pin) Female 1 - DVI-I (29 pin) Female 2 - USB 3.0 A (Fast-Charge, 9 pin) Female 3 - USB Type-A (9 pin) USB 3.0 Female 1 - RJ-45 Female 1 - 3.5 mm Mini-Jack (4 Position) Female 1 - USB Type-B (9 pin) USB 3.0 Female
<b>Software</b>	OS Compatibility	Windows® XP SP3 (32-bit), Vista, 7, 8, 8.1, 10 macOS 10.6 - 10.12, 10.14 - 10.15 Chrome OS™ v55+
<b>Special Notes / Requirements</b>	<b>Note</b>	HDMI and VGA adapters included VGA adapter can only be used on the DVI-I (29-pin) port The DVI-I connector supports DVI-I signaling (digital and analog)

		This USB docking station is not intended for graphical intensive applications, such as gaming
	System and Cable Requirements	USB 3.0 port interface and USB 3.0 cable to connect the Laptop Docking Station to a host computer (USB 3.0 host cable included)
<b>Indicators</b>	LED Indicators	1 - Power
<b>Power</b>	Center Tip Polarity	Positive
	Input Current	0.8 A
	Input Voltage	100 - 240 AC
	Output Current	2 A
	Output Voltage	12 DC
	Plug Type	H
	Power Consumption (In Watts)	24W
	Power Source	AC Adapter Included
<b>Environmental</b>	Humidity	5~85% RH
	Operating Temperature	0°C to 50°C (32°F to 122°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
<b>Physical Characteristics</b>	Cable Length	39.4 in [1000 mm]
	Color	Black & Silver
	Enclosure Type	Aluminum and Plastic
	Product Height	7 in [17.8 cm]
	Product Length	3.3 in [83 mm]
	Product Width	0.9 in [23 mm]
	Weight of Product	10.1 oz [285 g]
<b>Packaging Information</b>	Package Height	3.7 in [95 mm]
	Package Length	7.3 in [18.6 cm]
	Package Width	10 in [25.5 cm]
	Shipping (Package) Weight	2.2 lb [1 kg]
<b>What's in the Box</b>	Included in Package	1 - USB 3.0 Laptop Docking Station 1 - 1m USB 3.0 Cable 4 - Rubber Feet 1 - Stand

- 2 - Stand Screws
- 1 - Screwdriver
- 1 - DVI to VGA Adapter
- 1 - DVI to HDMI Adapter
- 1 - Universal Power Adapter (NA/JP, EU, UK, ANZ)
- 1 - Driver CD
- 1 - Instruction Manual

---

Product appearance and specifications are subject to change without notice.