

Dual Monitor USB 3.0 Docking Station with HDMI - DVI - 6 x USB Ports

Product ID: USB3SDOCKHD



This USB 3.0 dock combines a 6 port USB 2.0/USB 3.0 hub, headphone and microphone audio connectors, and a Gigabit Ethernet RJ45 port into a single docking station.

Display Adaptability

Offering flexible dual video combinations right out-of-the-box, this universal laptop docking station features HDMI and DVI external monitor output providing up to 1920x1200p resolutions, as well as an included DVI to VGA adapter for added flexibility.

Integrated USB Hub

The built-in USB hub features 2 USB 3.0 ports and 4 USB 2.0 ports for connecting extra peripherals such as external hard drives or a wired mouse as if they connected directly to your laptop.

Versatile Design

With an upright design, the dock occupies as little desk space as your smart phone, so it's perfect for hoteling or hot desk environments.

Direct Ethernet Connectivity

The integrated RJ45 Ethernet port supports speeds of 10/100/1000 Mbps, giving you an instant connection to a reliable wired network.

StarTech.com's laptop docking stations can be used for cost savings and faster deployment with just a single cable. This USB 3.0 Docking Station is backed by a competitive 3-year warranty and free lifetime multilingual Technical Support.

Certifications, Reports and Compatibility



Applications

- Shared workspaces
- Hot/Remote desks
- Convert laptop to desktop workstation

Features

- Connect dual monitors (HDMI and DVI) to your Mac or Windows laptop
- Achieve sharp resolution with 1920 x 1200p on dual displays
- Connect more devices with 6 USB ports - 2 x USB 3.0 and 4 x USB 2.0
- Setup your workstation anywhere and save space with the mobile upright design
- Connect to the networks with the built in 10/100/1000 Mbps compatible RJ45 Ethernet port

Hardware	Warranty	3 Years	
	4K Support	No	
	Bus Type	USB 3.0	
	Chipset ID	DisplayLink - DL-3900 VIA/VLI - VL810 Terminus - FE1.1 Realtek - RTL8211E	
	Displays Supported	2	
	Fast-Charge Port(s)	No	
	Industry Standards	IEEE 802.3, 802.3u, and 802.3ab	
Performance	Auto MDIX	Yes	
	Compatible Networks	10/100/1000 Mbps	
	Full Duplex Support	Yes	
	Maximum Digital Resolutions	1920 x 1200 Lower resolutions are also supported.	
	Type and Rate	USB 2.0 - 480 Mbit/s USB 3.0 - 5 Gbit/s	
Connector(s)	Connector Type(s)	1 - DVI-I (29 pin) Female 1 - HDMI (19 pin) Female 1 - RJ-45 Female 1 - USB Type-B (9 pin) USB 3.0 Female 2 - 3.5 mm Mini-Jack (3 Position) Female 2 - USB Type-A (9 pin) USB 3.0 Female 4 - USB Type-A (4 pin) USB 2.0 Female	
	Software	OS Compatibility	Windows® XP SP3 (32-bit), Vista, 7, 8, 8.1, 10 macOS 10.6 - 10.12, 10.14 Chrome OS™ v55+
	Special Notes / Requirements	Note	The DVI-I connector supports DVI-I signaling (digital and analog)
		System and Cable Requirements	CPU: i3 Dual core 2.8GHz or better RAM: 2GB or higher Available USB 3.0 port
	Indicators	LED Indicators	1 - Power (Blue) 1 - USB Hub Link (Blue)
		Power	Input Current

	Input Voltage	100 ~ 240 AC
	Output Current	4A
	Output Voltage	5 DC
	Plug Type	C
	Power Consumption (In Watts)	20
	Power Source	AC Adapter Included
Environmental	Operating Temperature	10°C to 40°C (50°F to 104°F)
	Storage Temperature	-10°C to 80°C (14°F to 176°F)
Physical Characteristics	Color	Black
	Enclosure Type	Plastic
	Product Height	7.7 in [19.5 cm]
	Product Length	4.9 in [12.5 cm]
	Product Width	2.8 in [70 mm]
	Weight of Product	13.1 oz [370 g]
Packaging Information	Package Height	4.3 in [10.9 cm]
	Package Length	10.7 in [27.3 cm]
	Package Quantity	1
	Package Width	7.5 in [19 cm]
	Shipping (Package) Weight	33.4 oz [947 g]
What's in the Box	Included in Package	1 - USB 3.0 Docking Station
		1 - 3.3 ft [1 m] USB 3.0 Cable
		1 - DVI to VGA Adapter
		1 - Universal Power Adapter (NA/JP, EU, UK, ANZ)
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.