

Dual-Monitor USB 3.0 Docking Station with HDMI & DVI/VGA

Product ID: USB3SDOCKHDV



This USB 3.0 dock combines three USB 3.0 ports, headphone and microphone audio connectors, and a Gigabit Ethernet RJ45 port, into a single docking station for maximum productivity.

Display Adaptability

Offering flexible dual video combinations right out-of-the-box, this universal laptop docking station features HDMI, DVI and VGA external monitor outputs. Each video output supports HD video resolutions (2048x1152 max) and HD video playback for an ideal solution to expanding your notebook's video capability.

Available display combinations:

- HDMI + VGA
- HDMI + DVI

Integrated USB Hub

The built-in USB hub features three USB 3.0 ports for connecting extra peripherals such as external hard drives or a wired mouse, as if they are connected directly to your laptop.

Direct Ethernet Connectivity

The integrated RJ45 Ethernet port supports speeds of 10/100/1000 Mbps, giving you an instant connection to a wired network.

StarTech.com laptop docking stations can be used for cost savings and faster deployment with just a single cable. This USB 3.0 Docking Station is backed by a competitive 3-year warranty and free lifetime Technical Support.

Certifications, Reports and Compatibility



Applications

- Shared workspaces
- Hot/Remote desks
- Convert laptop to desktop workstation

Features

- Connect dual monitors using either HDMI + DVI-D, or HDMI + VGA combinations
- Connect devices with 3 USB 3.0 ports
- Connect to wired networks with the built-in 10/100/1000 Mbps compatible RJ45 Ethernet port
- TAA compliant GSA schedule purchases

Hardware	Warranty	3 Years
	4K Support	No
	Bus Type	USB 3.0
	Chipset ID	DisplayLink - DL-3900 Genesys Logic - GL3520 Realtek - RTL8211E
	Displays Supported	2
	Fast-Charge Port(s)	No
	Industry Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3ab, USB 3.0
Performance	Audio Specifications	The HDMI port supports audio output
	Auto MDIX	Yes
	Compatible Networks	10/100/1000 Mbps
	Full Duplex Support	Yes
	Maximum Analog Resolutions	2048x1152 (VGA)
	Maximum Data Transfer Rate	5 Gbps (USB 3.0) 2 Gbps (Ethernet; Full-Duplex)
	Maximum Digital Resolutions	1920x1200 (DVI-D) 1920x1080 (HDMI) Lower resolutions are also supported.
Connector(s)	Type and Rate	USB 3.0 - 5 Gbit/s
	Connector Type(s)	1 - DVI-D (25 pin) Female
		1 - HDMI (19 pin) Female
		1 - RJ-45 Female
		1 - USB Type-B (9 pin) USB 3.0 Female
		1 - VGA (15 pin, High Density D-Sub) Female
		2 - 3.5 mm Mini-Jack (3 Position) Female
3 - USB Type-A (9 pin) USB 3.0 Female		
Software	OS Compatibility	Windows® XP SP3 (32-bit), Vista, 7, 8, 8.1, 10 macOS 10.6 - 10.12, 10.14
Special Notes / Requirements	System and Cable Requirements	Available AC electrical outlet
		HDMI (and either DVI-D or VGA if dual display is desired) enabled display device(s) e.g. monitor, projector, HTDV, etc. with cables USB 3.0 enabled computer system with available USB 3.0 port

Power	Center Tip Polarity	Positive
	Input Current	0.9 A
	Input Voltage	100 ~ 240 AC
	Output Current	4 A
	Output Voltage	5 DC
	Plug Type	B
	Power Consumption (In Watts)	20
	Power Source	AC Adapter Included
Environmental	Humidity	0~90% RH
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-10°C to 60°C (14°F to 140°F)
Physical Characteristics	Cable Length	3 ft [0.9 m]
	Color	Black
	Enclosure Type	Plastic
	Product Height	1.7 in [44 mm]
	Product Length	12 in [304 mm]
	Product Weight	10.4 oz [295 g]
	Product Width	7 in [178 mm]
Packaging Information	Shipping (Package) Weight	31 oz [878 g]
What's in the Box	Included in Package	1 - Docking Station
		1 - 0.9m USB 3.0 Cable
		1 - Universal Power Adapter (NA/EU/UK/AU)
		1 - Installation CD
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.