

2 Port USB 3.0 A Female Low Profile Slot Plate Adapter

Product ID: USB3SPLATELP



The USB3SPLATELP 2-Port USB 3.0 A Female Low Profile Slot Plate converts the USB pins on a USB 3.0 motherboard header to 2 standard USB 3.0 A-Style ports. An ideal solution for small form factor computer cases, the plate can be mounted on the rear panel of a low profile or thin client computer case, adding two USB 3.0-A female ports for simple connection to USB peripheral devices.

The USB3SPLATELP is ideal for small form factor computer cases.

The USB 3.0 standard supports transfer rates of up to 5Gbps, and provides connectivity and support for older USB 2.0 (480Mbps) and 1.1 (12Mbps) devices.

Certifications, Reports and Compatibility



Applications

- Add 2 USB 3.0-A Female ports to the back of a low profile or thin client type desktop PC, by extending an internal USB 3.0 motherboard header
- Ideal for small form factor computer cases

Features

- Two Superspeed USB 3.0-A Female ports

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
Connector(s)	Connector A	2 - USB Type-A (9 pin) USB 3.0 Female
	Connector B	1 - IDC (20 pin, USB 3.0, Motherboard Header) Female
Physical Characteristics	Cable Length	1.6 ft [0.5 m]
	Color	Blue
	Product Length	19.7 in [500 mm]
	Product Weight	2.3 oz [65 g]
	Wire Gauge	28 AWG
Packaging Information	Package Quantity	1
	Shipping (Package) Weight	2.5 oz [70 g]
What's in the Box	Included in Package	1 - 2 Port USB 3.0 A Female Low Profile Slot Plate Adapter

Product appearance and specifications are subject to change without notice.