

USB to Dual DisplayPort Mini Dock with GbE LAN - Dual 4K 60 Hz

Product ID: USBA2DPGB



This USB to Dual DisplayPort Mini Dock provides your USB 3.0 laptop with connectivity for dual 4K 60 Hz monitors and Gigabit LAN - enabling you to quickly harness dual-display productivity and network connectivity.

Increase Your Productivity with Two 4K Monitors

The dual DisplayPort adapter adds two DP video outputs to your USB laptop, with resolution support up to 4K. Working on two monitors increases your productivity by giving you more screen space. You can simultaneously access multiple applications and reference material on one display while composing on the other.

Access Hardwired Networks with a GbE Port

Ethernet ports on modern laptops are uncommon, and wireless networks are less secure and less reliable than a hardwired connection. With the GbE port on this portable docking station that features an Ethernet adapter you can access wired LANs even if your USB 3.0 laptop doesn't have an Ethernet port.

Maximize Portability with a Miniature Docking Station

The dock features a compact design that's perfect for business professionals who need portable office desk accessories for traveling between multiple office locations, or shared workspaces.

The USBA2DPGB is TAA compliant and backed by a 3-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Keep your docking station with your laptop while traveling
- Perform high-resolution tasks like graphic design or video editing on two 4K 60Hz monitors
- Connect to hardwired networks in offices that avoid wireless networks

Features

- Dock your USB 3.0 equipped Windows laptop with a portable USB docking station that supports dual monitors: 2x DisplayPort
- Get hardwired LAN connectivity to secure networks, with a dual DisplayPort adapter that features a Gigabit Ethernet port
- Take your connectivity on the go, with a compact mini dock that travels with your laptop
- TAA compliant and backed by a 3-year StarTech.com warranty

Hardware	Warranty	3 Years
	4K Support	Yes
	Bus Type	USB 3.0
	Chipset ID	DisplayLink - DL-6950
	Displays Supported	2
	Fast-Charge Port(s)	No
	Industry Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3ab USB 3.0 - Backward compatible with USB 2.0/1.1
Performance	Auto MDIX	Yes
	Compatible Networks	10/100/1000 Mbps
	Full Duplex Support	Yes
	Maximum Data Transfer Rate	5 Gbps (USB 3.0) 2 Gbps (Ethernet; Full-Duplex)
	Maximum Digital Resolutions	Dual displays - DisplayPort - 4096 x 2160 @ 60Hz / 3840 x 2160 @ 60Hz
	Type and Rate	USB 3.0 - 5 Gbit/s
	UASP Support	No
Connector(s)	Connector Type(s)	2 - DisplayPort (20 pin) Female 1 - RJ-45 Female 1 - USB Type-A (9 pin) USB 3.0 Male
Software	OS Compatibility	Windows® 7, 8, 8.1, 10 macOS 10.10 - 10.12, 10.14 - 10.15
Special Notes / Requirements	Note	USB 3.0 is also known as USB 3.1 Gen 1; this connectivity standard offers speeds up to 5Gbps. 4K resolution is supported on both video ports. A 4K-capable DisplayPort display is required to achieve 4Kx2K resolution.
	System and Cable Requirements	A host laptop with an available USB-A port.
Power	Power Source	USB-Powered
Environmental	Humidity	10-90% RH
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-10°C to 60°C (14°F to 140°F)
Physical Characteristics	Cable Length	5.5 in [140 mm]
	Color	Black

	Product Height	0.8 in [2 cm]
	Product Length	5.1 in [13 cm]
	Product Width	2.3 in [58 mm]
	Weight of Product	4.4 oz [126 g]
Packaging Information	Package Height	1.5 in [38 mm]
	Package Length	4.5 in [11.4 cm]
	Package Width	7.9 in [20 cm]
	Shipping (Package) Weight	7.6 oz [215 g]
What's in the Box	Included in Package	1 - mini dock 1 - quick-start guide

Product appearance and specifications are subject to change without notice.