

## VGA to USB-C Video Capture Device - 1080p 60fps

Product ID: USBC2VGCAPRO



This VGA to USB-C™ video capture device works as an external USB capture card to record high-definition VGA video to your USB-C, USB-A or Thunderbolt 3 computer. With an aluminum enclosure, this device is built strong for fixed-location or on-the-go capture. It offers a separate 3.5 mm audio input for accompanying audio or voice-overs, and a VGA pass-through port for connecting a monitor to review the video as it's captured.

### Easy Video Recording on Windows and Mac

The included software makes USB-C VGA capture easy by turning your computer into a VGA recorder. Using a widely adopted codec, videos saved in StreamCatcher™ work with almost any video player and require no converting or editing.

On Windows, you can live broadcast your video over the internet, using Twitch™ or other third-party video streaming platforms, with the included software.

## **Capture HD Video at 1080p 60fps**

With this VGA to USB video capture device, you can record meetings, presentations, conference calls and security footage, saving 1080p HD video at 60fps directly to your computer for easy editing and sharing.

## **DirectShow Compatibility on Windows**

With this VGA to USB 3.0 video capture device, you can record raw/lossless video using any third-party DirectShow™ compatible software, such as Open Broadcaster Software (OBS).

The USBC2VGCAPRO is backed by a 2-year StarTech.com warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Record video for training and tutorial purposes
- Capture live video by connecting the camera directly to the device
- Live stream the connected video source over the internet

### Features

- Hassle-free video recording with intuitive software included for Windows and macOS
- Seamless picture quality with USB 3.0 bandwidth enabling you to capture 1080p video at 60fps
- Platform freedom with DirectShow compatibility enabling you to use your preferred software

<b>Hardware</b>	Warranty	2 Years
	Audio	Yes
	AV Input	VGA
	AV Output	USB
	Chipset ID	Mstar - MST3363CNK-170
	Industry Standards	NTSC, PAL-M, PAL-60, PA Video Encoding: MPEG4 (H.264) DirectShow Compatible
<b>Performance</b>	Audio Specifications	2-channel stereo audio
	Maximum Analog Resolutions	1920 x 1080 60 FPS
	MTBF	2,543,711 Hours
	Supported Resolutions	1920 x 1080, 1280 x 720, 1024 x 768, 800 x 600
	Wide Screen Supported	Yes
<b>Software</b>	OS Compatibility	Windows® 7, 8, 8.1, 10 MacOS® 10.11 to 10.14
<b>Special Notes / Requirements</b>	<b>Note</b>	This video capture device requires a USB 3.0 port (or higher). The video capture device does not work with USB 2.0 ports (or lower).  The capture software included for macOS does not support video streaming
<b>Power</b>	Power Source	USB-Powered
<b>Environmental</b>	Humidity	20% to 80% (non-condensing)
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-5°C to 40°C (23°F to 105°F)
<b>Physical Characteristics</b>	Product Height	1 in [24.3 mm]
	Product Length	3.6 in [92.2 mm]
	Product Weight	3.6 oz [102 g]
	Product Width	2.4 in [61.1 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	1 lb [0.5 kg]
<b>What's in the Box</b>	Included in Package	1 - USB-C capture device 1 - 6 ft. [2m] USB-C to USB-B Cable 1 - 3.3 ft. [1m] USB-A to USB-B cable

1 - 3.3 ft. [1m] VGA cable

Product appearance and specifications are subject to change without notice.