

# USB-C to USB Data Transfer Cable for Mac and Windows - USB 3.0

Product ID: USBC3LINK



Transfer files from your old computer to your new USB-C enabled laptop or desktop computer, quickly over USB 3.0. This data transfer cable is easy to use and works with both Mac and Windows®.

## Save time setting up your new computer

The transfer cable saves you time and effort when you're upgrading from a USB-A computer to your new USB Type-C computer. You can quickly transfer your files and settings over USB 3.0, also known as USB 3.1 Gen 1, with file transfer speeds up to 5Gbps. There's no CD or download required - the software is stored on the cable so you're ready to go.

## Compatible with Mac and PC

As you're setting up your new computer, the USB 3.0 transfer cable offers wide compatibility letting you transfer files between two computers including Windows to Windows transfers, Windows to Mac, Mac to Windows, and even Mac to Mac transfers.

The cable is compatible with Windows Easy Transfer software for migrating to a newer version of Windows, up to Windows 8 (Windows 8.1 does not support data transfer cables.). The PCLinq software, stored on the cable, allows file transfers in any direction between any compatible OS, with no CD or download required.

### **Easy to use**

The transfer cable comes in a convenient 2 m length for ease of use.

The USBC3LINK is backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- When you upgrade to a new computer, migrate data and transfer files and settings from your older PC or Mac
- An easy solution for transferring documents, photos, music and other files to your new computer

### Features

- Transfer files to your new USB-C enabled laptop or computer quickly over USB 3.0 (5Gbps)
- Wide operating system support, works with Windows and Mac
- Compatible with Windows Easy Transfer software for migrating to newer version of Windows (up to Windows 8)
- PCLinq software, stored on the cable, allows file transfer in any direction between any compatible OS - no CD or download required
- Convenient 2 m cable length

<b>Hardware</b>	Warranty	2 Years
	Chipset ID	OTi - 7300
	Ports	1
<b>Performance</b>	Maximum Data Transfer Rate	5 Gbps
	Type and Rate	USB 3.0 - 5 Gbit/s
<b>Connector(s)</b>	Connector Type(s)	1 - USB Type-A (9 pin) USB 3.0 1 - USB Type-C (24 pin) USB 3.0
	<b>Software</b>	OS Compatibility
		<b>Note:</b> The provided PCLinq software is required in Windows 10, 8.1, and Mac OS. In Windows 10 and 8.1, Microsoft removed support for cables from the Windows Easy Transfer software.
<b>Indicators</b>	LED Indicators	2 - Link/Activity
<b>Environmental</b>	Humidity	5%RH ~ 90%RH
	Operating Temperature	0°C to 60°C (32°F to 140°F)
	Storage Temperature	-10°C to 80°C (14°F to 176°F)
<b>Physical Characteristics</b>	Cable Length	78.7 in [2000 mm]
	Color	Black
	Enclosure Type	Plastic
	Product Height	0.4 in [11 mm]
	Product Length	1.5 in [38.5 mm]
	Product Weight	1.4 oz [39.5 g]
	Product Width	0.9 in [23.5 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	1.8 oz [50 g]
<b>What's in the Box</b>	Included in Package	1 - data transfer cable
		1 - quick-start guide

Product appearance and specifications are subject to change without notice.