

4 Port USB A Female Slot Plate Adapter

Product ID: USBPLATE4



The USBPLATE4 4 port USB 2.0 slot plate adapter converts the USB pins on your motherboard into four USB-A female ports, enabling you to add USB connections to the back of your PC.

Backed by Lifetime Warranty, the USBPLATE4 is designed and constructed for maximum durability, to ensure dependable performance.

Please Note: Check your motherboard's manual for the USB pinout diagram. The USBPLATE wiring scheme is: Red=Power, Green=Signal, White=Signal, Black=Ground

Certifications, Reports and Compatibility



Applications

- Mount four USB-A female ports to the back of your PC by connecting them to 2x 4 or 5 pin IDC motherboard connections

Features

- 4x USB-A female ports
- 2x IDC 10-pin Female connectors
- Supports 4 or 5 pin motherboard connections
- Separate cables supports 2 rows of 4/5

	Warranty	Lifetime
Performance	Type and Rate	USB 2.0 - 480 Mbit/s
Connector(s)	Connector A	2 - IDC (10 pin, Motherboard Header) Female
	Connector B	4 - USB Type-A (4 pin) USB 2.0 Female
Environmental	Humidity	20%~60%
	Operating Temperature	-5°C to 40°C (41°F to 104°F)
	Storage Temperature	-5°C to 80°C (41°F to 176°F)
Physical Characteristics	Cable Length	11.3 in [286 mm]
	Product Weight	2.4 oz [68 g]
Packaging Information	Shipping (Package) Weight	0.2 lb [0.1 kg]
What's in the Box	Included in Package	1 - 4 Port USB 2.0 Connector Backplate

Product appearance and specifications are subject to change without notice.